




Dimensions

Technical data



Model Number

V15-G-ABG-PG9-FE

Female connector, M12, 5-pin, shielded, field attachable

Features

- Manufacturable, screenable
- Metal housing
- Iris spring screening
- Ground connection (FE) possible

General specifications		
Number of pins		5
Electrical specifications		
Operating voltage	U_B	max. 60 V DC
Operating current	Ι _Β	max. 4 A
Volume resistance		$<$ 3 m Ω
Ambient conditions		
Ambient temperature		-25 85 °C (-13 185 °F)
Pollution degree		3
Mechanical specifications		
Degree of protection		IP67
Connection		Screw terminals for max. 0.75 mm ² PG9 cable gland
Material		
Contacts		CuZn
Contact surface		Au
Body		Zinc die-casting, nickel-plated
Slotted nut		Zinc die-casting, nickel-plated
Cable		

5 ... 8 mm

EN 60529

Electrical connection

Compliance with standards and direc-

Sheath diameter

Standard conformity

Degree of protection

