

SMART Transmitter Power Supply KFD2-STC5-Ex1.20

- 1-channel isolated barrier
- 24 V DC supply (Power Rail)
- Input 2-wire and 3-wire SMART transmitters and 2-wire SMART current sources
- Signal splitter (1 input and 2 outputs)
- Dual output 4 mA ... 20 mA current sink/current source
- Terminals with test points
- Up to SIL 2 (SC 3) acc. to IEC/EN 61508













Function

This isolated barrier is used for intrinsic safety applications.

The device supplies 2-wire and 3-wire SMART transmitters, and can also be used with 2-wire SMART current sources.

It transfers the analog input signal to the safe area as two isolated output signals.

Digital signals may be superimposed on the input signal in the hazardous or non-hazardous area and are transferred bi-directionally.

The device provides a sink mode or a source mode output on the safe area terminals.

The device has an internal resistor. Use this resistor if the HART communication resistance in the control circuit is too low.


Test sockets for the connection of HART communicators are integrated into the terminals of the device.

Application

The device supports the following SMART protocols: • HART

- BRAIN
- Foxboro

Connection



Short circuit unused outputs decreases the internal power dissipation by up to 100 mW per channel.

Technical Data

General specifications		
Signal type	Analog input	
Functional safety related parameters		
Safety Integrity Level (SIL)	SIL 2	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"


Release date: 2023-06-05 Date of issue: 2023-06-05 Filename: 239214_eng.pdf

Technical Data		
Systematic capability (SC)		SC 3
Supply		
Connection		Power Rail or terminals 14+, 15-
Rated voltage	U_{r}	18 30 V DC
Ripple		within the supply tolerance
Power dissipation		≤ 1 W at maximum load
Power consumption		≤ 1.7 W at maximum load
Input		
Connection side		field side
Connection		terminals 1+, 2-, 3
Input signal		4 20 mA
Open circuit voltage/short-circuit current		terminals 1+, 3: 23 V / 25 mA
Input resistance		max. 265 Ω terminals 2-, 3 , max. 330 Ω terminals 1+, 3
Available voltage		\geq 16 V at 20 mA; \geq 20 V at 4 mA, terminals 1+, 3
Output		
Connection side		control side
Connection		terminals 7+, 8-, 9-; 10+, 11-, 12- (sink) terminals 7-, 8+, 9+; 10-, 11+, 12+ (source) see additional information
Load		0 600 Ω
Output signal		4 20 mA (overload > 25 mA)
Ripple		max. 50 μA _{rms}
External supply (loop)		2 30 V DC If the external voltage is > 19 V, a load \geq ((V - 19) / 0.02) Ω is required. V represents the value of the external voltage. The internal 250 Ω resistor at terminals 9 and 12 can be used as a load.
Transfer characteristics		
Deviation		at 20 °C (68 °F), 4 20 mA ≤ 10 µA incl. calibration, linearity, hysteresis, loads and fluctuations of supply voltage
Influence of ambient temperature		≤ 0.25 µA/K
Frequency range		field side into the control side: bandwidth with 0.5 V_{pp} signal 0 7.5 kHz (-3 dB) control side into the field side: bandwidth with 0.5 V_{pp} signal 0.3 7.5 kHz (-3 dB)
Settling time		200 μs
Rise time/fall time		100 μs
Galvanic isolation		
Output/power supply		functional insulation, rated insulation voltage 50 V AC
Output/Output		functional insulation, rated insulation voltage 50 V AC
Indicators/settings		
Display elements		LED
Labeling		space for labeling at the front
Directive conformity		
Electromagnetic compatibility		
Directive 2014/30/EU		EN 61326-1:2013 (industrial locations)
Conformity		
Electromagnetic compatibility		NE 21:2012 EN 61326-3-2:2008
Degree of protection		IEC 60529:2001
Protection against electrical shock		UL 61010-1:2012
Ambient conditions Ambient temperature		-20 60 °C (-4 140 °F) extended ambient temperature range up to 70 °C (158 °F), refer to manual for necessary mounting conditions
Mechanical specifications		necocodi y mounting conditions
Degree of protection		IP20
Connection		screw terminals
Mass		approx. 200 g
Dimensions		
DITHERISIONS		20 x 124 x 115 mm (0.8 x 4.9 x 4.5 inch) (W x H x D) , housing type B2

Technical Bata		
Mounting		on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in connection with hazar	dous a	reas
EU-type examination certificate		CML 17 ATEX 2031X
Marking		© II (1)G [Ex ia Ga] IIC © II (1)D [Ex ia Da] IIIC © I (M1) [Ex ia Ma] I
Input		[Ex ia Ga] IIC, [Ex ia Da] IIIC, [Ex ia Ma] I
Supply		
Maximum safe voltage	U_m	250 V (Attention! The rated voltage can be lower.)
Equipment		terminals 1+, 3-
Voltage	U_{o}	26.2 V
Voltage	U_q	27.25 V
Current	Io	93 mA
Power	P_o	634 mW
Equipment		terminals 2-, 3
Voltage	U_{i}	30 V
Current	l _i	115 mA
Power	P_i	max 1 W
Voltage	U_{\circ}	2 V
Current	Io	8.5 mA
Power	Po	4.3 mW
Equipment		terminals 1+, 2 / 3-
Voltage	U_{\circ}	26.2 V
Voltage	U_q	27.25 V
Current	Io	115 mA
Power	Po	784 mW
Certificate		CML 17 ATEX 3030X
Marking		
Galvanic isolation		
Input/Output		safe electrical isolation acc. to IEC/EN 60079-11:2007, voltage peak value 375 V
Input/power supply		safe electrical isolation acc. to IEC/EN 60079-11:2007, voltage peak value 375 V
Directive conformity		
Directive 2014/34/EU		EN IEC 60079-0:2018+AC:2020 , EN 60079-7:2015+A1:2018 , EN 60079-11:2012
International approvals		
UL approval		E106378
Control drawing		116-0439 (cULus)
IECEx approval		
IECEx certificate		IECEx CML 17.0016X
IECEx marking		[Ex ia Ga] IIC , [Ex ia Da] IIIC , [Ex ia Ma] I Ex ec IIC T4 Gc
General information		
Supplementary information		Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

Assembly

Front view



Matching System Components

KFD2-EB2	Power Feed Module
UPR-03	Universal Power Rail with end caps and cover, 3 conductors, length: 2 m
UPR-03-M	Universal Power Rail with end caps and cover, 3 conductors, length: 1,6 m
UPR-03-S	Universal Power Rail with end caps and cover, 3 conductors, length: 0.8 m
K-DUCT-BU	Profile rail, wiring comb field side, blue
K-DUCT-BU-UPR-03	Profile rail with UPR-03- * insert, 3 conductors, wiring comb field side, blue

Accessories

	KF-ST-5GN	Terminal block for KF modules, 3-pin screw terminal, green
	KF-STP-5GN	Terminal block for KF modules, 3-pin screw terminal, with test sockets, green
	KF-STP-5BU	Terminal block for KF modules, 3-pin screw terminal, with test sockets, blue
*	KF-CP	Red coding pins, packaging unit: 20 x 6