











Model Number

ML4.2-54-G/40b/95/110

Retroreflective sensor with 4-pin, M8 x 1 connector


Features

- High-precision sensors for complex applications
- Miniature design with very robust and versatile mounting options
- Optical surface made of scratchresistant glass for areas that are prone to high levels of dirt
- Reliable recognition of reflective objects and clear glass
- Two machines in one: clear object detection or reflection operating mode with long range
- TEACH-IN switch for setting the contrast detection levels
- Automatic adjustment in case of soiling in contrast detection mode


Product information

The ML4.2 series is characterized by a robust, powerful and standard design in a miniature housing. The housing offers IP67/ IP69K degree of protection, a scratch- and chemical-resistant lens, highly visible LEDs and robust all-metal bushings for mounting. Adjustable and tamper-proof sensors are available with a universal push-pull output and an electrical light ON/dark ON switch. The sensors have a high ambient light limit. Reflections from the background are suppressed. The unusually small, sharp light spot and the quick response time offer maximum switching precision on object edges.. Both red and infrared light sources are available. A high-performance fixed focus background suppressor is a useful feature. The sensors are suitable for precise object detection and open up a wide range of application

Dimensions



Electrical connection



- O = Light on
- = Dark on


Pinout

Wire colors in accordance with EN 60947-5-2

² 1 3

1 | BN (brown) 2 | WH (white) 3 | BU (blue) 4 | BK (black)

Indicators/operating means



2019-11-26

date:

Technical data		
General specifications		
Effective detection range		0 3.5 m in TEACH mode 0 5 m at switch position "N"
Reflector distance		0 3.5 m in TEACH mode 0 5 m at switch position "N"
Threshold detection range		6 m
Reference target		H85-2 reflector
Light source		LED
Light type		modulated visible red light, 660 nm
Polarization filter		yes
Angle deviation		max. ± 1°
Diameter of the light spot		approx. 40 mm at detection range 1 m
Angle of divergence		1.7 °
Ambient light limit		40000
Continuous light		40000 Lux 5000 Lux
Modulated light		5000 Lux
Functional safety related parame	eters	000 a
MTTF _d Mission Time (T _M)		980 a 20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		0 /0
Operation indicator		LED green, statically lit Power on , Undervoltage indicator:
Operation indicator		Green LED, pulsing (approx. 0.8 Hz) , short-circuit: LED green flashing (approx. 4 Hz)
Function indicator		LED yellow: switching state ; Stability control ; Teach-In
Control elements		5-step switch for setting the contrast detection levels.
Contrast detection levels		switch position I: 10 % - clean, water filled PET bottles switch position II: 18 % - clear glass bottles switch position III: 40 % - coloured glass or opaque materials adjustable due to Teach-In switch
Electrical specifications		
Operating voltage	U _B	10 30 V DC
Ripple		max. 10 %
No-load supply current	I ₀	< 15 mA at 24 V DC
Output		
Switching type		light/dark on electrically switchable , Pin 2 open or at 0V = light switching, Pin 2 at +UB = dark switching
Signal output		1 push-pull (4 in 1) output, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Voltage drop	U _d	≤ 2.5 V DC 1 kHz
Switching frequency		
Response time		500 μs
Conformity		EN 00047 F 0
Product standard		EN 60947-5-2
Ambient conditions		00 00 00 / 4 440 05\
Ambient temperature		-20 60 °C (-4 140 °F)
Storage temperature		-20 75 °C (-4 167 °F)
Mechanical specifications		10.0
Housing width		13.9 mm
Housing death		31.4 mm 18 mm
Housing depth Degree of protection		IP67 / IP69K
Connection		M8 x 1 connector, 4-pin
Material		Wo X 1 Connector, 4-pin
Housing		ABS
Optical face		glass pane
Mass		approx. 10 g
Compliance with standards and directives		
Standard conformity		
Shock and impact resistance		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions
Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -2000 Hz, 10 g in each X, Y and Z directions
Approvals and certificates		
CE conformity		yes
UL approval		cULus Listed
CCC approval		CCC approval / marking not required for products rated ≤36 V
• •		5 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1

Accessories

OMH-4.1

Mounting Clamp

OMH-ML6

Mounting bracket

OMH-ML6-Z

Mounting bracket

OMH-ML6-U

Mounting bracket

OMH-11-02 Aperture-V-H 0.5 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-04 Aperture-V-H 1.0 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-06 Aperture-V-H 1.5 mm

Slit diaphragm can be affixed for detecting very small parts

OMH-11-08 Aperture-V-H 2.0 mm

Slit diaphragm can be affixed for detecting very small parts

V31-GM-2M-PVC

Female cordset single-ended, M8, 4-pin, PVC cable

V31-WM-2M-PVC

Female cordset single-ended, M8, 4-pin, PVC cable

REF-H85-2

Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes

REF-C110-2

Reflector, round ø 84 mm, central mounting hole

REF-H60-2

Reflector with mounting holes

Reflector, rectangular 60 mm x 19 mm, mounting holes

OFR-100/100

Reflective tape 100 mm x 100 mm

Reflector, round ø 20.5 mm, selfadhesive

REF-A25

Reflector, round ø 25 mm, self-adhesive

REF-MH23

Reflector with Micro-structure, rectangular 23 mm x 13.8 mm, diagonal mounting hole

REF-CLIP50HT

Reflector, round ø 50 mm, snap-in, high temperature applications


REF-H50HT


Reflector, rectangular 50.9 mm x 50.9 mm, mounting holes, fixing strap


Other suitable accessories can be found at www.pepperl-fuchs.com


FPEPPERL+FUCHS

Curves/Diagrams









Additional information

Adjustment instructions for Teach-In operation:

Step	Switch	LED	LED	Time/	Explanations/
	position	green	yellow	frequency	comments
1	N	on	flashes	4/s	In switch position "N" directed towards reflector.
					Reflector detected without function reserve.
	N	on	on	-	In switch position "N" directed towards reflector.
					Reflector detected with function reserve (recommended).
	Т	off/on	on	200 ms	The selection of a new switch position is indicated by the green LED going out for a short time.
					This also applies to the selection of the other switch positions.
	Т	flashes	flashes	2.5 s	Slow alternating flashing: Teach-In process has been performed correctly .
					Max. duration of the Teach-In process: 2 s
	Т	flashes	flashes	8/s	Quick alternating flashing: Teach-In process has not been performed correctly . (e.g. receiver signal not sufficient, sensor not directed correctly towards reflector).
					Status is terminated by turning switch to position N.
3/1	1	on	on	-	Contrast detection 10 % is activated. (e.g. clean PET bottles filled with water)
3/2	II	on	on	-	Contrast detection 18 % is activated. (e.g. clear glass bottles)
3/3	III	on	on	-	Contrast detection 40 % is activated. (e.g. coloured glass or non-transparent materials)

5PEPPERL+FUCHS