

Universal Temperature Converter KFD2-UT2-Ex2-1

- 2-channel isolated barrier
- 24 V DC supply (Power Rail)
- Thermocouple, RTD, potentiometer or voltage input
- Usable as signal splitter (1 input and 2 outputs)
- Voltage output 0/1 V ... 5 V
- Configurable by PACTware
- Line fault (LFD) and sensor burnout detection
- Up to SIL 2 acc. to IEC/EN 61508 / IEC/EN 61511













Function


This isolated barrier is used for intrinsic safety applications.

The device converts the signal of a resistance thermometer, thermocouple, or potentiometer to a proportional output voltage.


The device converts the signal of a resistance infermioneter, thermocouple, or potentioneter to a proportional output voltage. The device can also be configured as a signal splitter.

The removable terminal block K-CJC-** is available as an accessory for internal cold junction compensation of thermocouples. A fault is signalized by LEDs acc. to NAMUR NE44 and a separate collective error message output. The device is easily configured by the use of the PACTware configuration software. For additional information, refer to the manual and www.pepperl-fuchs.com.

Connection








Technical Data

General specifications		
Signal type		Analog input
Functional safety related parameters		
Safety Integrity Level (SIL)		SIL 2
Supply		
Connection		terminals 14+, 15- or power feed module/Power Rail
Rated voltage	U_{r}	20 30 V DC
Ripple		within the supply tolerance
Power dissipation		≤ 0.8 W
Power consumption		max. 0.8 W

Release date: 2023-01-03 Date of issue: 2023-01-03 Filename: 248768_eng.pdf

Technical Data

Interface	
Programming interface	programming socket
Input	
Connection side	field side
Connection	terminals 1, 2, 3; 4, 5, 6
RTD	type Pt10, Pt50, Pt100, Pt500, Pt1000 (EN 60751: 1995) type Pt10GOST, Pt50GOST, Pt100GOST, Pt500GOST, Pt1000GOST (6651-94) type Cu10, Cu50, Cu100 (P50353-92) type Ni100 (DIN 43760)
Measuring current	approx. 200 μA with RTD
Types of measuring	2-, 3-wire connection
Lead resistance	max. 50Ω per line
Measurement loop monitoring	sensor breakage, sensor short-circuit
Thermocouples	type B, E, J, K, N, R, S, T (IEC 584-1: 1995) type L (DIN 43710: 1985) type TXK, TXKH, TXA (P8.585-2001)
Cold junction compensation	external and internal
Measurement loop monitoring	sensor breakage
Potentiometer	$0 \dots 20 \ k\Omega$ (2-wire connection), $0.8 \dots 20 \ k\Omega$ (3-wire connection)
Voltage	selectable within the range -100 100 mV
Input resistance	\geq 1 M Ω (-100 100 mV)
Output	
Connection side	control side
Voltage output	$0 \dots 5 \text{ V or } 1 \dots 5 \text{ V}$; output resistance: $\leq 5 \Omega$; load: $\geq 10 \text{ k}\Omega$
Connection	output I: terminals 7-, 8+ output II: terminals 10-, 11+
Fault signal	downscale 0 V or 0.5 V, upscale 5.375 V
Transfer characteristics	
Deviation	
After calibration	Pt100: \pm (0.06 % of measurement value in K + 0.1 K (4-wire connection)) thermocouple: \pm (0.05 % of measurement value in °C + 1 K (1.2 K for types R and S)) includes \pm 0.8 K fault of the cold junction compensation (CJC) mV: \pm 50 μ V potentiometer: \pm 0.05 % of full scale, (excludes faults due to lead resistance) output: 1 to 5 V output: \pm 4 mV from 0 to 103.1 % of span; 0 to 5 V output: \pm 4 mV from 0.3 to 102.5 % of span
Influence of ambient temperature	Pt100: \pm (0.0015 % of measurement value in K + 0.0075 % of span)/K ΔT_{amb} ') thermocouple: \pm (0.02 K + 0.005 % of measurement value in °C + 0.0075 % of span)/L ΔT_{amb} '), influence of cold junction compensation (CJC) included: mV: \pm (0.01 % of measurement value + 0.0075 % of span)/K ΔT_{amb} ') potentiometer: \pm 0.0075 % of span/K ΔT_{amb} ') ') ΔT_{amb} = ambient temperature change referenced to 23 °C (296 K)
Influence of supply voltage	< 0.01 % of span
Reaction time	worst case value (sensor breakage and/or sensor short circuit detection enabled) mV: 1.2 s, thermocouples with CJC: 1.4 s, thermocouples with fixed ref. temp: 1.4 s, 3 or 4-wire RTD: 1.1 s, 2-wire RTD: 920 ms, Potentiometer: 3-wire connection 2.8 s, 2-wire connection 2.25 s
Galvanic isolation	
Output/supply, programming input	functional insulation, rated insulation voltage 50 V AC There is no electrical isolation between the programming input and the supply. The programming cable provides galvanic isolation so that ground loops are avoided.
Indicators/settings	
Display elements	LEDs
Configuration	via PACTware
Labeling	space for labeling at the front
Directive conformity	
Electromagnetic compatibility	
Directive 2014/30/EU	EN 61326-1:2013 (industrial locations)
Conformity	
Electromagnetic compatibility	NE 21:2006
Degree of protection	IEC 60529:2001




5PEPPERL+FUCHS

Technical Data

Protection against electrical shock		UL 61010-1:2004
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Mechanical specifications		
Degree of protection		IP20
Connection		screw terminals
Mass		approx. 130 g
Dimensions		20 x 119 x 115 mm (0.8 x 4.7 x 4.5 inch) (W x H x D) , housing type B2
Mounting		on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in connection with haza	rdous a	reas
EU-type examination certificate		CESI 04 ATEX 143
Marking		 II (1)G [Ex ia Ga] IIC II (1)D [Ex ia Da] IIIC I (M1) [Ex ia Ma] I
Input		Ex ia
Inputs		terminals 1, 2, 3, 4, 5, 6 (for passive equipment)
Voltage U _o		9 V
Current I _o		22 mA
Power P _o		50 mW
Analog outputs, power supply, collective error		
Maximum safe voltage	U_{m}	250 V (Attention! This is not the rated voltage.)
Interface		
Maximum safe voltage	U_{m}	250 V (Attention! The rated voltage is lower.), RS 232
Certificate		TÜV 02 ATEX 1797 X
Marking		
Galvanic isolation		
Input/Other circuits		safe electrical isolation acc. to IEC/EN 60079-11, voltage peak value 375 V
Directive conformity		
Directive 2014/34/EU		EN 60079-0:2012+A11:2013 , EN 60079-11:2012 , EN 60079-15:2010 , EN 50303:2000
International approvals		
UL approval		
Control drawing		116-0410
CSA approval		
Control drawing		116-0314 (cCSAus) 116-0347
IECEx approval		
IECEx certificate		IECEX TUN 07.0003 IECEX CML 16.0126X
IECEx marking		[Ex ia Ga] IIC , [Ex ia Da] IIIC , [Ex ia Ma] I Ex nA IIC T4 Gc
General information		
Supplementary information		Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com.

5PEPPERL+FUCHS

Assembly



Matching System Components

<u>O</u> m	DTM Interface Technology	Device type manager (DTM) for interface technology
PACTware Y	PACTware 5.0	FDT Framework
	K-ADP-USB	Programming adapter with USB interface
	KFD2-EB2	Power Feed Module
	UPR-03	Universal Power Rail with end caps and cover, 3 conductors, length: 2 m
	UPR-03-M	Universal Power Rail with end caps and cover, 3 conductors, length: 1,6 m
	UPR-03-S	Universal Power Rail with end caps and cover, 3 conductors, length: 0.8 m
	K-DUCT-BU	Profile rail, wiring comb field side, blue
	K-DUCT-BU-UPR-03	Profile rail with UPR-03- * insert, 3 conductors, wiring comb field side, blue

Accessories

Release date: 2023-01-03 Date of issue: 2023-01-03 Filename: 248768_eng.pdf

(K-CJC-BU	Terminal block for cold junction compensation, 3-pin screw terminal, blue			

Accessories KF-ST-5GN Terminal block for KF modules, 3-pin screw terminal, green KF-ST-5BU Terminal block for KF modules, 3-pin screw terminal, blue KF-CP Red coding pins, packaging unit: 20 x 6