



# RFID Transponder


## IUC77-25L110-GBL 1000pcs

- Operating frequency 865 ... 928 MHz
- Complies with EPC Gen2 (ISO/IEC 18000-63)
- Robust, adhesive plastic label

RFID Transponder

**UK  
CA**

### Dimensions



### Technical Data

General specifications	
Operating frequency	865 ... 928 MHz
Polarization	linear
Memory	
Chip Type	Monza 4QT (Impinj)
Memory Bank 00 (Reserved)	64 Bit
Memory Bank 01 (EPC/UII)	128 Bit
Memory Bank 10 (TID)	96 Bit
Memory Bank 11 (User memory)	512 Bit
Read cycles	unlimited
Write cycles	> 100000
Data retention period	10 years
Directive conformity	
Radio equipment	
Directive 2014/53/EU	EN 302208
RoHS	
Directive 2011/65/EU (RoHS)	IEC/EN 63000

Release date: 2023-08-09 Date of issue: 2023-08-09 Filename: 256089\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PF** PEPPERL+FUCHS

## Technical Data

Standard conformity		
Degree of protection		EN 60529
RFID		ISO/IEC 18000-63
Ambient conditions		
Ambient temperature		-40 ... 85 °C (-40 ... 185 °F)
Storage temperature		-40 ... 95 °C (-40 ... 203 °F)
Mechanical specifications		
Housing length		110 mm
Housing width		25 mm
Housing height		0.2 mm
Degree of protection		IP67
Material		
Housing		Polyester with transparent protective laminate
Installation		Adhesive
In air		yes
Mass		1 g
Construction type		Label
Note		Packaging unit, 1000 pcs. on a roll

## Installation Conditions

The minimum bending radius of the transponder is 50 mm. Do not bend the transponder above this bending radius. Do not touch the area of the integrated circuit IC. The IC is a sensitive electrical component that can be damaged by excessive pressure.