

RFID Transponder

IPC11-12 50pcs




- Battery-free data carrier
- 40 bit fixcode free programmable
- Readable and writable from both sides
- Degree of protection IP68
- Packaging unit: 50 pieces

Data carrier



Dimensions



Technical Data

General specifications

Operating frequency	125 kHz
Transfer rate	2 kBit/s

Memory

Chip Type	Q5 (Atmel)
EEPROM	40 Bit
Read cycles	unlimited

Directive conformity

Radio equipment	
Directive 2014/53/EU	EN 300330
RoHS	
Directive 2011/65/EU (RoHS)	IEC/EN 63000

Standard conformity

Degree of protection	EN 60529
RFID	ISO/IEC 18000-2

Ambient conditions

Ambient temperature	-25 ... 85 °C (-13 ... 185 °F)
---------------------	--------------------------------

Release date: 2021-10-01 Date of issue: 2021-10-01 Filename: 261641_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 PEPPERL+FUCHS

Technical Data

Storage temperature	-40 ... 130 °C (-40 ... 266 °F) for 1000 hours ≤ 150 °C (423 K) for 24 hours -20 ... 160 °C (253 ... 433 K) for 100 x 10 minutes with transposition in 30 seconds
Mechanical specifications	
Housing height	2 mm
Housing diameter	12.4 mm
Degree of protection	IP68
Material	
Housing	PPS and Epoxy (black)
Installation	
In air	yes
Construction type	Cylindrical
Note	Packaging unit, 50-piece

Application

The transponder can be read and written from either side.

Release date: 2021-10-01 Date of issue: 2021-10-01 Filename: 261641_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com