

## Features

- Certified for ATEX and IECEx Zone 2/22
- UL listed for USA and Canada
- Galvanic isolation between input and output
- Provides an output power up to 80 W at 24 V DC
- Fully IP66 rated

## Application

The device is an apparatus certified for use in hazardous areas rated according to ATEX directive and IECEx Zones 2 and 22.

The device is an AC-DC power supply and supplies explosion-protected equipment in the hazardous area. The device provides an output voltage of 24 V DC based on 110 V AC/230 V AC input voltage.

The output power has a derating from 50 °C to 65 °C (80 W to 50 W).

The device is optimized for use with the following devices:






- Display Unit DPU1200-J2-\*
- Thin Client Unit TCU1200-J2-\*
- PC Unit PCU1200-J2-\*



<b>Supply</b>	
Input voltage	115/230 V AC , 50/60 Hz
Input current	max. 1.5/0.7 A
<b>Output</b>	
Output rated operating current	≤ 3.4 A
Voltage	24 V DC (SELV)
Power	80 W with derating
Power dissipation	15 W at 80 W output power
<b>Directive conformity</b>	
Electromagnetic compatibility	
Directive 2014/30/EU	EN 61326-1:2013 (industrial locations) ; EN 61000-6-4:2007+A1:2011
RoHS	
Directive 2011/65/EU (RoHS)	EN 50581:2012-09
<b>Ambient conditions</b>	
Operating temperature	-20 ... 65 °C (-4 ... 149 °F) with derating
Storage temperature	-20 ... 65 °C (-4 ... 149 °F)
Relative humidity	93% at 40°C, non-condensating, according to EN 60068-2-78
Shock resistance	18 shocks 15 g , 11 ms all axis, IEC 60068-2-27
<b>Mechanical specifications</b>	
Core cross-section	≤ 2.5 mm <sup>2</sup> (14 AWG)
Degree of protection	IP66
Material	
Housing	anodized aluminum
Mass	approx. 3.2 kg
Dimensions	245 mm x 122 mm x 58 mm
<b>Data for application in connection with hazardous areas</b>	
EU-Type Examination Certificate	BVS 16 ATEX E 097 X
Marking	ⓧ II 3G Ex ec q IIC T4 Gc ⓧ II 3D Ex tc IIIC T85°C Dc
Directive conformity	
Directive 2014/34/EU	EN 60079-0:2012+A11:2013, EN 60079-5:2015, EN 60079-7:2015, EN 60079-31:2014
<b>International approvals</b>	
UL approval	E492874
Approved for	Class I, Division 2, Groups A, B, C, D T4; Zone 2, Group IIC T4 Class II, Division 2, Groups F, G T4; Zone 22, Group IIIB T85 Class III; Zone 22, Group IIIA T85
IECEX approval	IECEX BVS 16.0063X
Approved for	Ex ec q IIC T4 Gc Ex tc IIIC T85°C Dc
Standards	IEC 60079-0:2011 , IEC 60079-5:2015 , IEC 60079-7:2015 , IEC 60079-31:2013

Release date 2018-12-21 14:50 Date of issue 2018-12-21 271722-100006\_eng.xml

Dimensions



Release date 2018-12-21 14:50 Date of issue 2018-12-21 271722-100006\_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com