



**Model Number**


**V1-G-BK10M-PUR-U/ABG-V1-G-Y**

Connecting cable, M12 to M12, PUR cable 2-pin

**Features**

- UL Recognized Component
- Knurled nut suitable for tool assembly
- Immunity to vibration, with mechanical latching
- Flame resistant cable
- Gold plated contacts
- Resistant to microbes and hydrolysis
- Halogen-free

**Dimensions**



**Technical data**

**General specifications**

Number of pins	5 + shield
Connection 1	socket
Construction type 1	straight
Threading 1	M12
Connection 2	Male connector
Construction type 2	straight
Threading 2	M12
UL File Number	E231213

**Electrical specifications**

Operating voltage	U <sub>B</sub>	max. 60 V AC/DC
Operating current	I <sub>B</sub>	max. 4 A
Volume resistance		< 5 mΩ


**Ambient conditions**

Ambient temperature	Body: -40 ... 90 °C (-40 ... 194 °F) cable, flexing: -20 ... 80 °C (-4 ... 176 °F) cable, fixed: -40 ... 80 °C (-40 ... 176 °F)
Pollution degree	3

**Mechanical specifications**

Contact elements	spring-loaded contact socket
Pin diameter	1 mm
Degree of protection	IP67 / IP68 / IP69k
Cable code	Li 9Y C 11Y 5 x 0.50
<b>Material</b>	
Contacts	CuSn / Au
Contact surface	Au
Body	socket TPU, transparent Male connector TPU, black
Cable	PUR
Slotted nut	Diecast zinc
Sleeve connector	Diecast zinc
Core insulation	PP
Cable	fine-strand, flexible
Sheath diameter	Ø 6 mm ± 0.15 mm
Bending radius	> 10 x cable diameter, appropriate for conveyor chains > 5 x cable diameter, fixed
Color	black
Number of cores	5
Core cross-section	0.5 mm <sup>2</sup>
Conductor construction	16 x 0.2 mm Ø
Shield	grid covering 85 %
Length	L 10 m
Flammability	
Contact carrier	94 HB

**Electrical connection**



Release date: 2019-04-08 10:43 Date of issue: 2019-04-12 263914\_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Housing	94 V-2
Cable	FT2
<b>Compliance with standards and directives</b>	
Standard conformity	
Degree of protection	EN 60529:2000
Standards	IEC 61076-2-101:2008
Flammability	Body: UL 94 Line: UL 1581 Section 1061; IEC 60332-1-2:2004
Halogen-free	IEC 60754-1:1994
<b>Approvals and certificates</b>	
UL approval	UL Recognized General purpose

**Accessories**

**MH V1-SCREWDRIVER**  
torque screwdriver (0.6 Nm)

**MH V1-BIT M12**  
plug-in cap M12

**V1/V3-LABELHOLDER**  
Label holder

**V1/V3-LABEL**  
Label plate

**MH V1-Holder**  
Modular universal holder for M12 connectors

**V1-CLIP**  
Unlocking protector for M12 connector

**V1-MARKING-RING-BLUE**  
Marking ring for M12 plug

**V1-MARKING-RING-GREEN**  
Marking ring for M12 plug

**V1-MARKING-RING-ORANGE**  
Marking ring for M12 plug

**V1-MARKING-RING-RED**  
Marking ring for M12 plug

**V1-MARKING-RING-WHITE**  
Marking ring for M12 plug

**V1-MARKING-RING-YELLOW**  
Marking ring for M12 plug

Release date: 2019-04-08 10:43 Date of issue: 2019-04-12 263914\_eng.xml