

Laser light sensor VLM350-F280-R4-1101

- Resolution 1280 x 960 pixel
- Comparison of up to 32 height profiles
- Output of X/Z offset
- Intelligent exposure time control
- Laser class 1, eyesafe
- Data Matrix control codes for parameterization


Laser light sensor for profile matching; Comparison of up to 32 height profiles; Output of X/Z offset; Resolution: 1280 x 960 pixel; Measuring range: $X = 40 \dots 160 \text{ mm}$, $Z = 60 \dots 350 \text{ mm}$; Scan rate: 30 s-1; 2 digital outputs; RS-485 interface





Function


The SmartRunner Matcher compares current height profiles with a previously taught-in height profile. The Matcher is based on innovative SmartRunner technology and combines the light section method for detecting height profiles with a 2-D vision sensor. The light section method involves projecting a laser line onto an object. This is then detected by a camera at a specific angle. A height profile is then created using the triangulation principle. This innovative laser technology provides reliable measurements on different surfaces.

Dimensions









Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Technical Data

General specifications		V 10 100 mm 7 00 050 mm
Measurement range		X = 40 160 mm ; Z = 60 350 mm
Light source		laser diode
Light type		red laser + Integrated LED lightning red 650 nm
Laser nominal ratings		
Note		VISIBLE LASER RADIATION , DO NOT STARE INTO BEAM DO NOT VIEW DIRECTLY WITH OPTICAL INSTRUMENTS
Laser class		1
Wave length		Measuring laser: 660 nm
Pulse length		Measuring laser: 0.5 ms
Maximum optical power output		Measuring laser: 15 mW
Laser monitoring		The safety system switches off the laser when the laser current is too high
Scan rate		30 s ⁻¹
Resolution		X>0.25 mm; Z>0.2 mm at 60 mm distance X>0.5 mm; Z>0.6 mm at 200 mm distance X>0.9 mm; Z>1.3 mm at 350 mm distance
Functional safety related parameters		
MTTF _d		20 a
Mission Time (T _M)		10 a
Diagnostic Coverage (DC)		0%
Indicators/operating means		
Operation indicator		LED green
Diagnostics indicator		LED yellow / red
Function indicator		Trigger: LED yellow ; object detected : LED red / green
Control elements		2 push-buttons
Electrical specifications		
		24 V ± 20 % , PELV
Operating voltage	U _B	
No-load supply current		max. 250 mA
Power consumption Interface	P ₀	max. 6 W , Outputs without load
Interface type		RS 485 interface
Physical		Switchable terminal resistor
Protocol		binary code
Transfer rate		38400 230400 Bit/s
Input		
Input voltage		24 V
Number/Type		External triggering + 1 Input
Switching threshold		low: < 2.5 V, high: > 8 V
Output		
Number/Type		2 digital outputs
Switching type		PNP
Switching voltage		24 V
Switching current		150 mA each output
Compliance with standards and directives		
Standard conformity		
Noise immunity		EN 61000-6-2:2005
Emitted interference		EN 61000-6-4:2007/A1:2011
Degree of protection		EN 60529
Shock and impact resistance		EN 60068-2-27:2009
Laser class		IEC 60825-1:2007
Approvals and certificates		
UL approval		cULus Listed, Type 1 enclosure
CCC approval		CCC approval / marking not required for products rated \leq 36 V

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"


Pepperl+Fuchs Group www.pepperl-fuchs.com Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Technical Data	
Approvals	CE
Ambient conditions	
Operating temperature	-20 45 °C (-4 113 °F), (noncondensing; prevent icing on the lens!)
Storage temperature	-20 70 °C (-4 158 °F)
Mechanical specifications	
Housing width	38 mm
Housing height	85 mm
Housing depth	55 mm
Degree of protection	IP67
Connection	8-pin, M12 x 1 connector (supply + RS485 + Inputs/Outputs) ; can be rotated 90 $^\circ$; Grounding : Grounding clip for PCV system
Material	
Housing	PC/ABS
Optical face	Plastic pane
Mass	approx. 125 g
Tightening torque, fastening screws	max. 2 Nm
General information	
Note	Security Instructions: - Read the operating instructions before attempting commissioning - Installation, connection and adjustments should only be undertaken by specialist personnel - Not a safety component in accordance with the EU Machinery Directive

Connection

Pin	Signal			
1 2 3 4 5 6 7 8	IN Trigger +UB Data+ RS-485 Data- RS-485 Teach Good GND Bad			

Assembly



Poody	green/red
neauy	green/leu
Match 3/4	green/yellow
Result	green/red
Match 1/2	green/yellow
Diagnose	red
Power	green
Teach	yellow
Trigger	yellow
	Result Match 1/2 Diagnose Power Teach

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

Safety Information

CLASS 1 LASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007


Accessories

ø /	V19-G-5M-PUR-ABG	Female cordset single-ended M12 straight A-coded, 8-pin, PUR cable grey, shielded
	VLX-MB2	Mounting bracket
	VLX-MB1	Mounting bracket
	PCV-USB- RS485-Converter Set	USB to RS 485 interface converter
	V19-G-BK0,6M-PUR-U- V1-G-SRMAT	Cordset for SmartRunner Matcher, M12 to M12, 8/4-pin, PUR cable
F	VLX-F231-B6	Interface module with PROFIBUS interface for SmartRunner
	VLX-F231-B17	Interface module with PROFINET interface for SmartRunner
	VLX-F231-B21	Interface module with EtherCAT interface for SmartRunner
	VLX-F231-B25	Interface module with EtherNet/IP interface for SmartRunner
	VLX-F280-C	Weld slag cover model
	VLX-F280-C-GLASS	Replacement glass for SmartRunner protective housing

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Installation Conditions

Measuring range



Safety Information



LASERLICHT LASER LIGHT

LASER KLASSE 1 CLASS 1 LASER PRODUCT

Safety Information

Laser Class 1 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people!

Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

The warning accompanies the device and should be attached in immediate proximity to the device.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"