




Padlockable Shroud (Ex e) CFP.ZDT.SP

- SS316L shroud, padlockable
- Ex e certified
- Stainless Steel
- Component for appropriately certified Ex e enclosures

Emergency stop padlockable SS316L shroud, cover-mounted with type of protection Ex e

Dimensions



Dimension values see data table.

Image and drawing are generic for this device type and may deviate from the specific variant.

Technical Data

Electrical specifications

Function	Emergency stop padlockable shroud, cover-mounted
Color	Silver

Mechanical specifications

Degree of protection	IP66
Material	Stainless steel 1.4401 / AISI 316
Mass	97 g
Dimensions	
External dimension (A)	53 mm
External dimension (B)	70 mm
External dimension (C)	39.5 mm
Internal dimension (D)	40 mm
Internal dimension (E)	40 mm
Internal dimension (F)	4.2 mm
Tightening torque	1.3 ... 1.5 Nm
Mounting	use with base-mounted and cover-mounted contact modules

Ambient conditions

Ambient temperature	-40 ... 55 °C (-40 ... 131 °F)
---------------------	--------------------------------

Data for application in connection with hazardous areas

EU-type examination certificate	CML 16 ATEX 3339U
---------------------------------	-------------------

Release date: 2026-05-07 Date of issue: 2026-05-07 Filename: 290174_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

General information		
Supplementary information	For more information please contact Pepperl+Fuchs.	
Enclosure type		LR* SR*.CS* GR.CS*

Release date: 2026-05-07 Date of issue: 2026-05-07 Filename: 290174_eng.pdf