

Handheld reader OHV1000-F223-R2

- All common 1-D or 2-D codes can be read
- Dual lens for large read range
- Reading of laser-engraved, etched, or printed codes
- Reads from reflective surfaces
- Programmable with JavaScript
- Audible, tactile, and visual user feedback
- Degree of protection IP54


Handheld reader for reading lasered, punched or printed 1-D and 2-D codes




Function

The OHV1000 handheld is a compact handheld reader for all common 1-D and 2-D codes applied directly to the surface of a product. For example, the code may have been etched, printed, or laser-engraved on the housing. Special technology to prevent glare allows the device to accurately read codes on highly reflective surfaces. With its patented dual lens and a resolution of 1.2 million pixels, it can read both small and large codes from a wide range of distances. Feedback comes in the form of a visual or audible signal or a vibration. Using the Vision Configurator software, rule sets can be created for formatting read results without the need for extensive programming work. This facilitates integration into ERP systems. Data is transferred via USB or RS-232, depending on which connection cable is selected. With its robust housing and IP54 protection, the handheld reader is ideally suited to heavy-duty industrial use. Handheld reader OHV1000-F223-R2

Dimensions





Technical Data

General specifications	
Light type	Integrated LED lightning (red)
Readable codes	1-D Codes: Codabar, Code 11, Code 32, Code 39, Code 93, Code 128, IATA 2 of 5, Interleaved 2 of 5, GS1 DataBar, Hong Kong 2 of 5, Matrix 2 of 5, MSI Plessey, NEC 2 of 5, Pharmacode, Plessey, Straight 2 of 5, Telepen, Trioptic, UPC/EAN/JAN Stacked 1-D Codes: GS1 Composite, MicroPDF, PDF417 2-D Codes: Aztec Code, Code 49, Codablock F, Data Matrix, Han Xin, MaxiCode, Micro QR, QR Code Postal Codes: Australian Post, Intelligent Mail, Japan Post, KIX Code, Korea Post, Planet, Postnet, UK Royal Mail, UPU ID-tags
Read distance	0 200 mm depending on the code type and reading mode
Modul size	min. 0.1 mm
Ambient light limit	96890 Lux
Target velocity	Stop
Nominal ratings	
Camera	
Туре	CMOS
Number of pixels	1280 x 960
Image recording	real-time , manually triggered
Indicators/operating means	
Function indicator	LED green: Data carrier read
Electrical specifications	
Supply	via cable
Interface	
Physical	USB 2.0 , RS-232

Technical Data

Ambient conditions		
Ambient temperature	-20 55 °C (-4 131 °F)	
Storage temperature	-30 65 °C (-22 149 °F)	
Relative humidity	5 95 % non-condensing	
Shock and impact resistance	Withstands multible drops from 1.8 m / 6 ft onto a concrete surface	
Mechanical specifications		
Degree of protection	IP54	
Connection	System connector for connecting cable	
Material		
Housing	plastic	
Mass	130 g	
Dimensions	93 mm x 53 mm x 151 mm (l x w x h)	
General information		
Scope of delivery	Handheld reader	


Connection

Pin	Signal	
1	+VIN	
2	USB_DM	
3	USB_DP	
4	RS 232 TX	
5	RS 232 RTS	
6	RS 232 RX	
7	RS 232 CTS	
8	External Trigger	
9	not connected	
10	Ground	

Connection Assignment



Assembly



1	Mounting bracket
2	Function indicator
3	10-pin connector socket
4	Trigger button
5	Optics

Accessories



Release date: 2022-10-17 Date of issue: 2022-10-17 Filename: 272204_eng.pdf

Vision Configurator Operating software for camera-based sensors

V45-G-2M-PVC-ABG-

Adapter cable, RJ50 to USB





Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Accessories V45-G-2M-PVC-SUBD9 Adapter cable, RJ50 to RS 232 V50-G-2M-PVC-5V-Adapter cable, RJ-50 to D-Sub 25 SUBD25 **OHV1000-BRACKET** Bracket for OHV1000-F223-R2 V19S-G-1,7/3M-PVC-V50 Adapter cable, M12 8-pin to RS 232 OHV-F230-B17 PROFINET Gateway for OHV handheld