



LED Module Ex e, Cover-mounted CFP.GE.SP



- 10 ... 28 V AC/DC
- Component for appropriately certified Ex e enclosures
- Mounting on enclosure cover
- Ex de certified
- Polyamide



Dimensions



Dimension values see data table.
Image and drawing are generic for this device type and may deviate from the specific variant.

Technical Data

Electrical specifications

Operating voltage	28 V max. AC/DC
Power consumption	1 W max.
Terminal capacity	2.5 mm ²
Terminal torque	0.8 Nm
Function	LED module
Rated operating voltage	10 ... 28 V AC/DC

Mechanical specifications

Degree of protection	IP20
Material	
Housing	Polyamide (PA)
Mass	71 g
Dimensions	
External dimension (A)	54 mm
External dimension (B)	37 mm

Release date: 2025-06-12 Date of issue: 2025-06-14 Filename: 290228_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

External dimension (C)	63 mm
Total length (L)	88 mm
Mounting	cover-mounted via actuator head
Ambient conditions	
Service temperature	-40 ... 90 °C (-40 ... 194 °F)
Data for application in connection with hazardous areas	
EU-type examination certificate	CML 16 ATEX 3339U
Marking	Ⓔ II 2 G Ex de IIC Gb
International approvals	
IECEX approval	IECEX CML 16.0114U
Conformity	
Degree of protection	EN 60529
General information	
Supplementary information	EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com .
Enclosure type	SR.CS*