
Capacitive sensor

CBN15-F64-A2-V31-Y290300



- 15 mm non-flush
- Flat housing
- Switching distance adjustable between 2 mm ... 15 mm

Dimensions



Technical Data


General specifications		
Switching function		complementary
Output type		PNP
Rated operating distance	s_n	15 mm
Installation		non-flush
Output polarity		DC
Assured operating distance	s_a	0 ... 10.8 mm
Actual operating distance	s_r	13.5 ... 16.5 mm
Output type		4-wire
Nominal ratings		
Installation conditions		
B		15 mm
C		30 mm
F		45 mm / 60 mm
Operating voltage	U_B	10 ... 30 V DC
Switching frequency	f	0 ... 100 Hz
Hysteresis	H	1 ... 10 % typ. 5 %
Reverse polarity protection		reverse polarity protected

Release date: 2026-02-26 Date of issue: 2026-02-26 Filename: 290300_eng.pdf

Technical Data

Short-circuit protection		pulsing I_{max} ≤ 500 mA
Voltage drop	U_d	≤ 2 V
Repeat accuracy	R	≤ 1.5 mm
Operating current	I_L	0 ... 100 mA
Off-state current	I_r	0 ... 50 µA typ. 5 µA
No-load supply current	I_0	≤ 15 mA
Switching state indicator		LED, yellow
Safety-relevant product characteristics		
$MTTF_d$		941 a
Mission Time (T_M)		20 a
Diagnostic Coverage (DC)		0 %
Indicators/operating means		
Potentiometer		sensitivity adjustment
Compliance with standards and directives		
Standard conformity		
Standards		EN IEC 60947-5-2
Approvals and certificates		
UL approval		cULus Listed Circuitry: Class 2 Power Source Enclosure Type Rating: Type 1 Supply/Switching Voltage: 30 V DC Output Switching Current: 100 mA
CCC approval		CCC approval / marking not required for products rated ≤36 V
Ambient conditions		
Ambient temperature		-25 ... 70 °C (-13 ... 158 °F)
Storage temperature		-40 ... 85 °C (-40 ... 185 °F)
Pollution degree		3
Mechanical specifications		
Connection type		Connector plug
Housing material		PBT
Sensing face		PBT
Degree of protection		IP67
Connector		
Threading		M8 x 1
Number of pins		4
Tightening torque, housing screws		≤ 2 Nm
Dimensions		
Height		12 mm
Width		25 mm
Length		40 mm
Note		Screw-in depth of housing screws, max. 8 mm

Connection Assignment



Release date: 2026-02-26 Date of issue: 2026-02-26 Filename: 290300_eng.pdf


Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Installation Conditions



Release date: 2026-02-26 Date of issue: 2026-02-26 Filename: 290300_eng.pdf