

34.4

FDA ECOLAB

Model Number

V1-WV4A-5M-PP-H1

Single-ended female cordset, M12, V4A stainless steel, hygienic design, 4-pin, PP cable

Features

- Suitable for applications involving contact with products in the food and beverage industry
- · Certified by ECOLAB
- Resistant to all common acid and alkaline cleaning products and disinfectants
- Degree of protection IP67 / IP68 / IP69
- · Suitable for drag chains
- Halogen-free (PVC-free)
- · Materials used compliant with FDA
- Hygenic design in accordance with EHEDG

Accessories

MH V1-SCREWDRIVER

torque screwdriver (0.6 Nm)

MH V1-BIT M12-W14-HEX

Plug-in attachment for M12 with hex stainless steel knurled nut

Technical data

Dimensions

General specifications	
Number of pins	4
Connection 1	socket
Construction type 1	right angle
Threading 1	M12
Connection 2	cable end

Electrical specifications

Operating voltage	U_B	max. 250 V AC/DC
Operating current	l _P	max. 4 A

Ambient conditions

Contact elements

Ambient temperature	cable, flexing: -25 105 °C (-13 221 °F)
	cable, fixed: -40 105 °C (-40 221 °F)

Pollution degree 3

Mechanical specifications

Degree of protection	1707 / 1708 / 1709
Material	
Contacts	CuSn
Contact surface	Ni/Au
Body	PP
Cable	PP-EPDM
Slotted nut	stainless steel V4A
Seal	FKM
Core insulation	PP
Temperature resistance	Cold bending-resistant and cold impact-resistant up to -40 $^{\circ}\text{C}$ (40 $^{\circ}\text{F})$

spring-loaded contact socket

Cable	extra-fine wire, flexible
Shooth diameter	Ø 1.7 mm

Bending radius > 10 x cable diameter, moving > 5 x cable diameter, fixed

ColorgreyCores $4 \times 0.34 \text{ mm}^2$ Conductor construction $42 \times 0.1 \text{ mm } \emptyset$

Length L 5 m

Drag chain suitability
Drag chain cycles ≥ 4000000
Motion velocity ≤ 3 m/s

 $\begin{tabular}{lll} Motion velocity & \le 3 m/s \\ Traverse distance & 10 m \\ Acceleration & \le 10 m/s^2 \\ Torsion cycles & \ge 4000000 \\ Torsional stress & \pm 270 \ ^\circ/m \\ Tightening torque, cable gland & 0.4 ... 0.6 Nm \\ Mating cycles & \ge 100 \\ \end{tabular}$

Electrical connection





www.pepperl-fuchs.com

Compliance with standards and directives

Standard conformity	
Degree of protection	EN 60529
Standards	IEC 61076-2-101
Halogen-free	IEC 60754-1
Temperature resistance	DIN EN 60811-1-4
Material	FDA-compliant in accordance with FDA 21 CFR 177,2600

2