



Retroreflective sensor with polarization filter



ML100-54-7346/59/103/115a/154

- No controls
- Miniature design
- Easy to use
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- Very bright, highly visible light spot
- Full metal thread mounting
- Not sensitive to ambient light

Retroreflective sensor with polarization filter








Function

The optical sensors of this series are suitable for both standard and demanding applications.

The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.


Dimensions





Technical Data **General specifications** Effective detection range 0 ... 3.5 m Reflector distance 0.01 ... 3.5 m Threshold detection range 4.5 m Reference target H50 reflector LED Light source Light type modulated visible red light Polarization filter Diameter of the light spot approx. 350 mm at a distance of 4.5 m Opening angle approx. 4° Optical face frontal Ambient light limit EN 60947-5-2:2007+A1:2012 Functional safety related parameters MTTF_d 860 a Mission Time (T_M) 20 a Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on Function indicator LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted **Electrical specifications** Operating voltage U_{B} 10 ... 30 V DC Ripple max. 10 % < 20 mA No-load supply current I_0 Output Switching type dark-on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector max. 30 V DC Switching voltage Switching current max. 100 mA, resistive load Voltage drop U_{d} ≤ 1.5 V DC 1000 Hz Switching frequency Response time $0.5 \, \mathrm{ms}$ Conformity Product standard EN 60947-5-2 Approvals and certificates cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -30 ... 60 °C (-22 ... 140 °F) Ambient temperature -40 ... 70 °C (-40 ... 158 °F) Storage temperature Mechanical specifications Housing width 11 mm Housing height 31 mm Housing depth 20 mm **IP67** Degree of protection Connection 300 mm fixed cable with M8 connector, 3-pin Material Housing PC (Polycarbonate) **PMMA** Optical face approx. 20 g 0.6 Nm Tightening torque, fastening screws 0.3 m Cable length

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


1 BN (brown) 3 BU (blue) 4 BK (black)

Indication




1	Signal display	yellow
2	Operating display	green

Characteristic Curve



Characteristic Curve



Accessories

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
A SHE		
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket
	OMH-10	Mounting aid for ML100 series
**	OMH-F10-ML100	Mounting aid for ML100 series
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole
	REF-H60-2	Reflector with mounting holes
	REF-H33	Reflector with screw fixing

Accessories				
	OFR-70-2	Reflective tape 70 mm x 70 mm		
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes		
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap		
	OFR-100/100	Reflective tape 100 mm x 100 mm		
6/	V3-GM-2M-PUR	Female cordset single-ended M8 straight A-coded, 3-pin, PUR cable grey		
61	V3-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 3-pin, PUR cable grey		