



- High chemical resistance
- Low weight
- Self-adhesive mounting
- High temperature resistance
- High mechanical stability

## Dimensions



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Technical Data

|                         |                                                                                                                                                                                          |
|-------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Material                | polyester laminate                                                                                                                                                                       |
| Surface                 | polyester , matte                                                                                                                                                                        |
| Mass                    | 6.3 g / m                                                                                                                                                                                |
| Tensile strength        | ≥ 150 N                                                                                                                                                                                  |
| Manufacturing tolerance | ± 1 mm/m                                                                                                                                                                                 |
| Adhesive                | Acrylate-based adhesive ; curing 72 h                                                                                                                                                    |
| Adhesive strength       | Average values (FTM2)<br>Aluminum : 24 N / 25 mm<br>High grade stainless steel : 25 N / 25 mm<br>ABS : 22 N / 25 mm<br>PP : 18 N / 25 mm<br>HD-PE : 12 N / 25 mm<br>LD-PE : 12 N / 25 mm |
| Note                    | Max. code tape length of 100 m per roll                                                                                                                                                  |

## Type Code

### Structure of the type code (Ordering information)

|   |   |   |     |     |     |     |     |     |   |   |   |   |   |   |   |     |     |     |     |     |     |
|---|---|---|-----|-----|-----|-----|-----|-----|---|---|---|---|---|---|---|-----|-----|-----|-----|-----|-----|
| P | C | V | (1) | (1) | (1) | (1) | (1) | (1) | M | - | A | A | 2 | 0 | - | (2) | (2) | (2) | (2) | (2) | (2) |
|---|---|---|-----|-----|-----|-----|-----|-----|---|---|---|---|---|---|---|-----|-----|-----|-----|-----|-----|

| PCV | Sensor Type                          |
|-----|--------------------------------------|
| PCV | Data Matrix positioning system (PCV) |

| (1) (1) (1) (1) (1) (1) | Length of the code tape            |
|-------------------------|------------------------------------|
| 1 ... 010000            | Total length of the code tape in m |

| M | Length unit |
|---|-------------|
| M | Meter       |

| AA | Code type                             |
|----|---------------------------------------|
| A  | Data Matrix ECC200, Symbol size 16x16 |
| A  | Absolute tape                         |

| 20 | Width of the code tape |
|----|------------------------|
| 20 | 25 mm (2 row version)  |

| (2) (2) (2) (2) (2) (2) | Start position                          |
|-------------------------|-----------------------------------------|
| 0 ... 009999            | Starting position of the code tape in m |