
Inductive sensor NSN8-18GM50-2E2-M1-S2D2

- No unusable area
- 8 mm non-flush
- Use of standard metallic actuating surfaces
- Applications up to Cat. 2, PLd/SIL 2 possible (can be used redundantly up to Cat. 3, PLe/SIL 3)
- LED for switching state and fault indication
- Safety outputs OSSD
- E1-Type approval
- Extended temperature range
- -40 ... +85 °C
- TÜV certified
- 10 V DC ... 30 V DC supply voltage

Function

The inductive safety sensors are TÜV-certified in accordance with the EU Machinery Directive, Performance Level PLd, Category 2, and SIL2. They are used to safeguard machines and plant components, as well as for reliable position detection in this environment. With their OSSD interface for reliable, redundant shutdown of electronic outputs, they enable easy connection to a safety PLC or fail-safe control interfaces. They can also be operated as standard sensors. The sensors reliably detect standard metal objects in front of the sensor face without coding or similar; there is no blind zone. High characteristic safety values allow longer testing intervals than comparable solutions with a microcontroller. 2 sensors can be connected with 2-channel redundancy and allow PLe as a Category 3 solution.

Dimensions



Technical Data

General specifications		
Switching function		2 x normally open (NO)
Output type		PNP
Rated operating distance	Sn	8 mm
Installation		non-flush
Output polarity		DC
Assured operating distance	Sa	0 6.48 mm
Actuating element		Reference target according EN IEC 60947-5-2 (FE360 - ST37K) 24 mm x 24 mm x 1 mm
Reduction factor r _{AI}		0.5

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com


Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



0.5
0.85
0.55
4-wire
10 30 V
12 24 V
030 Hz
typ. 5%
reverse polarity protected
pulsing
yes
≤3 V
at I _L (sum of all outputs) max. 50 mA
1 30 mA per output 0 0.5 mA
≤ 15 mA ≤ 300 ms
LED, yellow
LED, red
SIL 2
PLd
Cat. 2
> 7500 a
20 a min. 60 %
12 mm
EN IEC 60947-5-2:2007 EN IEC 60947-5-3:2013 EN ISO 13849-1:2015 EN IEC 61508:2010 EN IEC 62061:2021 compatible with EN ISO 61131-2:2007 Typ 1, 2, 3
cULus Listed, General Purpose, Class 2 Power Source
CCC approval / marking not required for products rated \leq 36 V
10R-06
-40 85 °C (-40 185 °F)
-40 85 °C (-40 185 °F)
≤ 2000 m above MSL
cable PUR , 2 m
0.5 mm ²
brass, nickel-plated
PBT
IP68 / IP69
107 g
S

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Connection



Commissioning

Note for Setting the Safety Control The sensor has a self-monitoring function for the outputs. Therefore, to avoid any malfunctions of the sensor, deactivate all test pulses of the connected safety controller to the sensor.

Access	sories	
	BF 18	Mounting flange, 18 mm

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3