

Thru-beam sensor (pair) LD28/LV28-LAS-F1-7675



- Universal series with highly versatile fields of use
- Resistant against noise: reliable operation under all conditions
- Highly visible LED as alignment aid in receiver optics
- Emitter with test input
- Laser version for long ranges

Universal thru-beam sensor, large housing design, 120 m detection range, red laser light, laser class 2, 25 kHz transmission frequency, light/dark on, DC version, push-pull output, test input, pre-fault output, M12 plug












Dimensions



Technical Data


System components



Technical Data		
Emitter		LD28-LAS-F1-7675
Receiver		LV28-LAS-F1-7675
General specifications		
Effective detection range		0 120 m
Threshold detection range		150 m
Light source		laser diode
Light type		modulated visible red light
Laser nominal ratings		· ·
Note		LASER LIGHT , DO NOT STARE INTO BEAM
Laser class		2
Wave length		650 nm
Beam divergence		< 4 mrad
Pulse length		20 μs
Repetition rate		25 kHz
max. pulse energy		18 nJ
Alignment aid		LED red (in receiver lens) illuminated constantly: beam is interrupted,
		flashes: reaching switching point, off: sufficient stability control
Diameter of the light spot		Approx. 20 mm at 5 m, approx. 75 mm x 300 mm at 70 m horizontal in relation to the housing axis
Opening angle		Emitter: 0.23 ° Receiver: 5 °
Ambient light limit		50000 Lux
Functional safety related parameters		
MTTF _d		540 a
Mission Time (T _M)		20 a
Diagnostic Coverage (DC)		90 %
Indicators/operating means		
Operation indicator		LED green
Function indicator		LED yellow: 1. LED lit constantly: signal > 2 x switching point (function reserve) 2. LED flashes: signal between 1 x switching point and 2 x switching point 3. LED off: signal < switching point
Control elements		sensitivity adjustment (Adjustment to < 25% of the effective operating range) , Lighton/dark-on changeover switch
Electrical specifications		
Operating voltage	U_B	10 30 V DC
Ripple		10 %
No-load supply current	I ₀	Emitter: ≤ 55 mA Receiver: ≤ 40 mA
Input		
Test input		emitter deactivation at +U _B
Output		
Stability alarm output		1 PNP transistor, short-circuit protected, protected from reverse polarity, open collector, Umax = 30 V DC, Imax = 0.2 A The output becomes inactive if the signal level has fallen below the function reserve for approx. 10 s (yellow and red LEDs flash). If the light beam is interrupted four times during this period, the output immediately becomes inactive.
Switching type		light/dark on, switchable
Signal output		1 push-pull (4 in 1) output, short-circuit protected, reverse polarity protected
Switching voltage		max. 30 V DC
Switching current		max. 100 mA
Switching frequency	f	1000 Hz
Response time	f	1000 Hz 0.5 ms
	f	
Response time	f	

Approvals and certificates	
Protection class	II, rated voltage ≤ 250 V AC with pollution degree 1-2 according to IEC 60664-1
UL approval	cULus Listed , Class 2 power source
CCC approval	CCC approval / marking not required for products rated ≤36 V
FDA approval	IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviation pursuant to Laser Notice No. 50, dated June 24, 2007
Ambient conditions	
Ambient temperature	0 40 °C (32 104 °F)
Storage temperature	-20 75 °C (-4 167 °F)
Mechanical specifications	
Housing width	25.8 mm
Housing height	88 mm
Housing depth	54.3 mm
Degree of protection	IP67
Connection	5-pin, M12 x 1 plastic connector
Material	
Housing	Plastic ABS
Optical face	Plastic pane
Mass	140 g (emitter and receiver)

Connection Assignment




- O = Light on
- = Dark on


Connection Assignment



1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)
5 GY (gray)

Characteristic Curve





LUMIÈRE LASER
NE PAS REGARDER LE FAISCEAU
PRODUIT LASER CLASSE 2
LONGUEUR D'ONDE: 650 nm
MAX. ÉNERGIE D'IMPULSION: < 18 nJ
DURÉE D'IMPULSION: 20 µs CERTIFIÉ CEI 60825-1: 2007.
CONFORME AUX NORMES 21 CFR
1040, 10 ET 1040,111 À L'EXCEPTION
DES ÉCARTS CONFORMÉMENT
À LA NOTICE DU LASER
N° 50, DATÉE DU 24 JUIN 2007.

Safety Information

Laser Class 2 Information
The irradiation can lead to irritation especially in a dark environment. Do not point at people!
Caution: Do not look into the beam!

Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Accessories

6.9	OMH-05	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-21	Mounting bracket: mounting aid for sensors in the RL* series
	OMH-22	Mounting aid for RL* series
	OMH-RLK29-HW	Mounting bracket for rear wall mounting
	OMH-RL28-C	Weld slag cover model
6 /	V15-G-2M-PUR	Female cordset single-ended M12 straight A-coded, 5-pin, PUR cable grey