

Technical data


Dimensions

General specifications		
Number of pins		4
Connection 1		Male connector
Construction type 1		straight
Threading 1		M12
Connection 2		cable end
Electrical specifications		
Operating voltage	UB	max. 250 V AC/DC
Operating current	I _B	max. 4 A
Volume resistance		< 5 mΩ
Ambient conditions		
Ambient temperature		-25 80 °C (-13 176 °F)
Mechanical specifications		
Pin diameter		1 mm
Degree of protection		IP67 when sealing with O-Ring
Connection		Single strand leads with connector sleeves
Material		
Contacts		CuZn
Contact surface		Au
Connector		plastic
Seal		NBR
Core insulation		PVC
Cable		
Number of cores		4
Core cross-section		0.25 mm ²
Length	L	80 mm
Installation		Front mounting PG9
Compliance with standards and direc- tives		
Standard conformity		
Degree of protection		EN 60529

Notes

O-ring (13,3 x 1,5) and lock nut are included and assembled.

Electrical connection



1 🖛	 BN
2	 WH
3 🗕	 BU
4 🗖	 BK

Model Number

V1S-K-PG9P-90

Receptacles, M12/PG9, 4-pin; plastic version

Features

- · Plastic version
- Front/screw mounting ٠
- M12 plug can be mounted in any posi-٠ tion

Accessories

V1S-B Blind plug for M12 sockets

Refer to "General Notes Relating to Pepperl+Fuchs Product Information" USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 4411 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com

