




Control code tape

PGV*-CC25-*

- High chemical resistance
- Low weight
- Self-adhesive mounting
- High temperature resistance
- High mechanical stability

Control code tape für PGV System

Dimensions



Technical Data

General specifications	
Start marker number	1 ... 999
Number	1 ... 999
Length	1 m per control code number
Width	25 mm (1 row version)
Ambient conditions	
Operating temperature	-40 ... 100 °C (-40 ... 212 °F)
Installation temperature	10 ... 40 °C (50 ... 104 °F)
Environmental resistance	UV radiation Humidity Salt spray (150 h / 5%)
Chemical resistance	Oils Grease Fuels Aliphatic solvents Weak acids
Mechanical specifications	
Material thickness	150 µm
Material	polyester laminate

Release date: 2023-06-22 Date of issue: 2023-06-22 Filename: 299655_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Technical Data

Surface	polyester , matte
Mass	6.3 g / m
Tensile strength	≥ 150 N
Manufacturing tolerance	± 1 mm/m
Adhesive	Acrylate-based adhesive ; curing 72 h
Adhesive strength	Average values (FTM2) Aluminum : 24 N / 25 mm High grade stainless steel : 25 N / 25 mm ABS : 22 N / 25 mm PP : 18 N / 25 mm HD-PE : 12 N / 25 mm LD-PE : 12 N / 25 mm

Additional Information

Example for order information

Control codes **150** to **199** are required. The order is placed using the start number for the number range and the end number for the number range.

This results in the order designation **PGV-CC25-150-050-SET**. The number **50** in the order designation represents the number of control code strips each measuring 1 m. The number **150** in the order designation represents the start number.

NOTE: Control code numbers from 1 ... 999 can be ordered as required. In this example, the delivery consists of 50 control code strips, each measuring 1 m long. The control code tape is 1-meter long and can also be shortened if required. Please note that, depending on the travel speed and the measuring rate of the read head, the control code tape must have a minimum length to be detected reliably.

Type Code

Structure of the type code (Ordering information)

P	G	V	-	C	C	2	5	-	(1)	(1)	(1)	(1)	(1)	-	(2)	(2)	(2)	(2)	(2)	-	S	E	T
---	---	---	---	---	---	---	---	---	-----	-----	-----	-----	-----	---	-----	-----	-----	-----	-----	---	---	---	---

PGV	Sensor Type
PGV	Position Guided Vision







CC	Code type
C	Data Matrix ECC200, Symbol size 12x12
C	Control code

25	Width of the control code tape
25	25 mm

(1) (1) (1) (1) (1)	Start control code no.
00001 ... 00999	Start number of the control code tape

(2) (2) (2) (2) (2)	Number
00001 ... 00999	Number of control code strips, each 1 m long.

Matching System Components

	PGV100RS-F213-R4-1.5M	Read head for incident light positioning system
	PGV100R-F213-R4-1.5M	Read head for incident light positioning system
	PGV100-F200A-B25-V1D-8438	Read head for incident light positioning system
	PGV150I-F200-B16-V15	Read head for incident light positioning system
	PGV100R-F200-B16-V15-8482	Read head for incident light positioning system
	PGV100R-F200-B16-1,5M-7800	Read head for incident light positioning system

Release date: 2023-06-22 Date of issue: 2023-06-22 Filename: 299655_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com





















USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Matching System Components

	PGV100RS-F200-B16-1,5M-8606	Read head for incident light positioning system
	PGV100RS-F200-B16-1,5M	Read head for incident light positioning system
	PGV100R-F200-B16-1,5M	Read head for incident light positioning system
	PGV100R-F200-B16-1,5M-KOL	Read head for incident light positioning system
	PGV100RS-F213-B16-1.5M	Read head for incident light positioning system
	PGV40RS-F213-B16-1.5M	Read head for incident light positioning system
	PGV40R-F213-B16-1.5M	Read head for incident light positioning system
	PGV100R-F213-B16-1.5M	Read head for incident light positioning system
	PGV100-F200A-B16-V15	Read head for incident light positioning system
	PGV100-F200A-B16-V15-8438	Read head for incident light positioning system
	PGV100-F200A-B17-V1D	Read head for incident light positioning system
	PGV100-F200A-B25-V1D	Read head for incident light positioning system
	PGV100-F200A-B6-V15B	Read head for incident light positioning system
	PGV100-F200A-R4-V19	Read head for incident light positioning system
	PGV100-F200A-R4-V19-6829	Read head for incident light positioning system
	PGV100-F200-B17-V1D-7477	Read head for incident light positioning system
	PGV100-F200-R4-V19	Read head for incident light positioning system
	PGV100I-F200-B16-V15	Read head for incident light positioning system
	PGV100I-F200A-R4-V19	Read head for incident light positioning system
	PGV100SI-F200A-R4-V19	Read head for incident light positioning system








Release date: 2023-06-22 Date of issue: 2023-06-22 Filename: 299655_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".



Pepperl+Fuchs Group
www.pepperl-fuchs.comUSA: +1 330 486 0001
fa-info@us.pepperl-fuchs.comGermany: +49 621 776 1111
fa-info@de.pepperl-fuchs.comSingapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Matching System Components

	PGV100SI-F200A-R4-V19-7941	Read head for incident light positioning system
	PGV150I-F200A-B17-V1D	Read head for incident light positioning system
	PGV150I-F200A-B25-V1D	Read head for incident light positioning system
	PGV150I-F200A-R4-V19	Read head for incident light positioning system
	PGV100R-F200-R4-1,5M	Read head for incident light positioning system
	PGV100R-F200-B16-V15-7666	Read head for incident light positioning system
	PGV100R-F200-B16-CJD	Read head for incident light positioning system

Accessories

	PGV25M-CD160-CLEAR	Protective laminate for PGV code tape
	PGV25M-CD100-CLEAR	Protective laminate for PGV code tape