


Model Number

V1SD-G-1M-PUR-ABG-V1SD-G
 Ethernet bus cable, M12 to M12, PUR cable 4-pin, CAT5e

Features

- D coding for Ethernet
- CAT5/CAT5e cable
- Hard-wearing PUR cable
- Halogen-free
- Completely silicon free
- Knurled nut suitable for tool assembly
- Immunity to vibration, with mechanical latching
- Shield attached to coupling nut


Dimensions



Technical data

General specifications		
Number of pins		4 + shield
Connection 1		Male connector
Construction type 1		straight
Threading 1		M12
Coding 1		D-coded
Connection 2		Male connector
Construction type 2		straight
Threading 2		M12
Coding 2		D-coded
Electrical specifications		
Operating voltage	U_B	max. 48 V AC / 60 V DC
Operating current	I_B	max. 4 A
Volume resistance		150 mΩ/m
Ambient conditions		
Ambient temperature		Body: -25 ... 90 °C (-13 ... 194 °F) cable, fixed: -40 ... 80 °C (-40 ... 176 °F) cable, flexing: -20 ... 80 °C (-4 ... 176 °F)
Pollution degree		3
Mechanical specifications		
Degree of protection		IP67 / IP68 / IP69
Connection		2 x M12 x 1 connector, 4-pin, D-coded
Material		
Contacts		CuZn
Contact surface		Ni/Au
Body		TPU, black / PA
Cable		PUR
Sleeve connector		Zinc die-casting, nickel-plated
Core insulation		PE
Cable		2 pairs with 2 wires each with 2 fillers for the core
Sheath diameter		6.7 mm
Bending radius		> 8 x cable diameter, moving > 4 x cable diameter, fixed
Color		water blue (RAL 5021)
Number of cores		4
Core cross-section		0.14 mm ²
Cores color		Core 1: white/orange Core 2: orange Core 3: white/green Core 4: green
Conductor construction		7 x 0.15 mm Ø
Shield		aluminum-lined polyester foil Tinned copper braiding, 70 % coverage
Length	L	1 m

Electrical connection



Release date: 2019-12-19 10:32 Date of issue: 2019-12-19 302274_eng.xml

Compliance with standards and directives

Standard conformity	
Degree of protection	EN 60529
Standards	CAT5 (IEC 11801:2002) , CAT5e (TIA 568B:2001)
Flammability	IEC 60332-1-2
Halogen-free	IEC 60754-1
Chemical resistance	DIN EN 60811-2-1
Specification	connector M12 x 1 : IEC 61076-2-101

Release date: 2019-12-19 10:32 Date of issue: 2019-12-19 302274_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".