


Glass fiber optic
LLR 04-1,6-1,0-G(M6x30)



- Chemical-resistant

Glass fiber optic - diffuse with metal silicone covering

Dimensions



Technical Data

General specifications		
Fiber optic length	l	1000 mm
Fiber optic diameter	d	7.3 mm
Adapter form		04
End piece		thread
Bending radius		min. 20 mm
Fiber bundle diameter		1.6 mm optical face: 2 mm²
Fiber configuration	Fv	optical seperated
Opening angle		approx. 68 °
Ambient conditions		
Ambient temperature		-20 ... 85 °C (-4 ... 185 °F) [Adapter] -40 ... 180 °C (-40 ... 356 °F) [End head and Covering]
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)
Mechanical specifications		
Degree of protection		IP65
Material		
Optical face		glass

Release date: 2025-12-17 Date of issue: 2025-12-17 Filename: 415671_eng.pdf

Technical Data

Sheathing		Metal-silicon
Core		Glass fiber
End piece		Stainless steel 1.4305 / AISI 303
Adapter		PVC
Extraction force		at probe at 20°C: 120 N
Fiber optic amplifiers		
Device series		MLV41-LL

Release date: 2025-12-17 Date of issue: 2025-12-17 Filename: 415671_eng.pdf

Application

Attention:
Fiber optics must not be twisted or kinked. Excessive tensile loads will lead to destruction. Contact with petrol or organic solvents must be prevented.



Release date: 2025-12-17 Date of issue: 2025-12-17 Filename: 415671_eng.pdf