



Print mark contrast sensor DK20/35A/9S20



- Diffuse mode sensor for recording any print mark
- Static TEACH-IN: automatic switching threshold adaptation
- Optical system exchangeable by 90°
- 30 µs response time, suitable for extremely rapid scanning processes
- 3 emitter colors: green, red and blue

Print mark contrast sensor, 25 mm detection range, RGB light with rectangular light spot, light/dark on, external Teach-in, timer function, push-pull output, M12 plug



Function

The contrast sensor series DK10, DK2X, DKE2X and DK3X have an extreme robust and IP67 tight industrial standard housing with eight M5 metal reinforced inserts for sensor mounting. The lenses are made of high grade glass. All sensors offer different light spot shapes and orientations and have powerful push-pull outputs (NPN/PNP/push-pull).


The DK10 sensor series offers laser and LED light sources, a manual sensitivity adjustment and high sensing ranges up to 800 mm.

The DK20/DK21/DKE2X standard contrast sensor series offers a very good contrast recognition and are available in extreme robust stainless-


steel housings (DKE).
The DK31/DK34/DK35 sensor series is designed for cutting edge contrast recognition at highest sensitivity level.
The series DK20/DK34 offer a static Teach-In, the DK21/DKE21/DK31/DK35 series offer a dynamic Teach-In.



Dimensions



	sensor range 9.5 mm	sensor range 25 mm		
Standard	1 mm x 4 mm	2 mm x 8.5 mm		
Option /A	□ 4 mm x 1 mm	8.5 mm x 2 mm		
Option /B	O Ø 1.5 mm	⊘ ø3 mm		




Technical Data


General specifications					
Sensor range		25 mm ± 6 mm			
Light source		LED			
Light type		Visible green/red/blue, modulated light			
Light spot representation		2 mm x 8.5 mm , light spot parallel to housing			
Angle deviation		max. ± 3°			
Ambient light limit					
Continuous light		7000 Lux			
Teach-In		static Teach-In			
Functional safety related parameters					
MTTF _d		650 a			
Mission Time (T_M)		20 a			
Diagnostic Coverage (DC)		0 %			
Indicators/operating means					
Function indicator		LED yellow; switching operation: lights up if print mark is detected Teach-In operation: flashing slowly alarm display: flashing quickly, if no safe operation is possible			
Control elements		Teach-In key			
Electrical specifications					
Operating voltage	U_B	10 30 V DC			
Ripple		10 %			
No-load supply current	I_0	≤ 70 mA			
Input					

Function input		Teach-In input			
Output					
Switching type		light/dark on switchable, results from the order of the Teach-In			
Signal output		Push-pull output, short-circuit protected, reverse polarity protected			
Switching voltage		$PNP: \ge (+U_B - 2.5 \text{ V}), NPN: \le 1.5 \text{ V}$			
Switching current		max. 200 mA			
Switching frequency	f	16.5 kHz			
Response time		30 μs			
Timer function		rising edge , mono stable			
Pulse length		20 ms			
Conformity					
Product standard		EN 60947-5-2			
Compliance with standards and directives					
Standard conformity					
Shock and impact resistance		IEC / EN 60068. half-sine, 40 g in each X, Y and Z directions			
Vibration resistance		IEC / EN 60068-2-6. Sinus. 10 -150 Hz, 5 g in each X, Y and Z directions			
Approvals and certificates					
EAC conformity		TR CU 020/2011			
UL approval		cULus Listed , Class 2 power source			
CCC approval		CCC approval / marking not required for products rated ≤36 V			
Ambient conditions					
Ambient temperature		-20 60 °C (-4 140 °F)			
Storage temperature		-20 75 °C (-4 167 °F)			
Mechanical specifications					
Housing width		33 mm			
Housing height		85.6 mm			
Housing depth		60.8 mm			
Degree of protection		IP67			
Connection		5-pin, M12 x 1 connector			
Material					
Housing		PC (glass-fiber-reinforced Makrolon)			
Optical face		glass			
Mass		200 g			

Connection Assignment







Accessories

	V15-G-5M-PVC	Female cordset single-ended M12 straight A-coded, 5-pin, PVC cable grey
	V15-W-5M-PVC	Female cordset single-ended M12 angled A-coded, 5-pin, PVC cable grey
H +	OMH-DK	Right-Angled Mounting Bracket
ŦŦ	OMH-DK-1	Flat Mounting Bracket

Additional Information

Construction

This device is supplied with a changeable Lens. By interchanging Lens and cover the sensor is able to be modified from a side-looker to a top-looker and vice versa.

Adjustment

- 1. Point the light spot to the print mark. With mirroring or shiny object surface the sensor has to be tilt by 10° ... 15°.
- 2. Press Teach-In key at the device or apply a positive pulse (UB+) for at least 50 ms to the external Teach-In input. After finishing this first step, the indicator LED flashes slowly (approx. 1 Hz).
- Point light spot to the underground/background.
- 4. Press Teach-In key or apply Teach-In signal once more.
- If Teach-In successful: sensor in switching mod, LED off.
 Alarme-Function: insufficient contrast. No reliable switching operation possible. Indicator LED flashes fast (approx. 4 Hz)
- 6. Return to switching mode when pressing key

The switching signal level is set automatically to the middle between print mark and background.

If there is the same contrast between mark and background for various transmitter colours, the sensor selects a transmitter colour by random.

For exact contrast evaluation the DK..., as an option, can be delivered with an additional analogue output.