

Retroreflective sensor

MPP6HD

- Harsh duty
- Withstands 1200 psi washdown
- Polarization filter to detect shiny objects
- Sensing range 4.5 m

Photoelectric Sensors; MP Series Modular

Technical Data

General specifications	
Sensing range	4.5 meters
Light source	Visible red
Light type	Visible red
Polarization filter	yes
Marking	CE
Indicators/operating means	
Function indicator	2 LEDs
Control elements	light on / dark on
Output	
Response time	≤ 1 ms
Output 1	
Output type	dependent on base selected
Standard conformity	
Standards	EN 60947-5-2
Approvals and certificates	
Approvals	CE, cULus
Ambient conditions	
Ambient temperature	-30 ... 70 °C (-22 ... 158 °F)
Storage temperature	-55 ... 85 °C (-67 ... 185 °F)
Relative humidity	95% RH (non-condensing)
Shock resistance	50G
Vibration resistance	10G, 10 ... 500 Hz
Mechanical specifications	
Degree of protection	IP69K
Material	
Housing	Polycarbonate
Optical face	Glass Lens
Sheathing	Glass-filled acetal, Type 20
Dimensions	
Height	43.2 mm
Width	39.6 mm
Depth	52.3 mm

Release date: 2024-07-10 Date of issue: 2024-07-10 Filename: 454433_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**