

Retroreflective sensor with polarization filter



ML100-54/59/82a/103/115a/154

- Miniature design
- Stability alarm indication
- Clearly visible LEDs for Power ON, switching state and weak signal indication
- No controls
- Very bright, highly visible light spot
- Full metal thread mounting

Retroreflective sensor with polarization filter








Function

The optical sensors of this series are suitable for both standard and demanding applications.

The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions






Technical Data

General specifications Effective detection range 0 ... 3.5 m Reflector distance 0.01 ... 3.5 m Threshold detection range 4.5 m Reference target H50 reflector LED Light source Light type modulated visible red light Polarization filter Diameter of the light spot approx. 350 mm at a distance of 4.5 m Opening angle approx. 4° Optical face frontal Ambient light limit EN 60947-5-2:2007+A1:2012 Functional safety related parameters $MTTF_d$ 860 a 20 a Mission Time (T_M) Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on Function indicator LED yellow: lights up when receiving the light beam; flashes when falling short of the operating reserve; OFF when light beam is interrupted **Electrical specifications** Operating voltage U_{B} 10 ... 30 V DC Ripple max. 10 % < 20 mA No-load supply current I_0 Output Stability alarm output 1 PNP, active when falling short of the stability control Switching type Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC Switching current max. 100 mA, resistive load; stability alarm output max. 50 mA Voltage drop U_{d} ≤ 1.5 V DC Switching frequency f 1000 Hz Response time 0.5 ms Conformity EN 60947-5-2 Product standard Approvals and certificates cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -30 ... 60 °C (-22 ... 140 °F) Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) Mechanical specifications Housing width 11 mm Housing height 31 mm Housing depth 20 mm IP67 Degree of protection Connection 300 mm fixed cable with M8 connector, 4-pin Material PC (Polycarbonate) Housing Optical face **PMMA** approx. 20 g 0.6 Nm Tightening torque, fastening screws Cable length 0.3 m

Connection




Connection Assignment



Wire colors in accordance with EN 60947-5-2


1 BN (brown)
2 WH (white)
3 BU (blue)
4 BK (black)


Indication



1	Signal display	yellow
2	Operating display	green

Characteristic Curve





T = 2 s

FR = function reserve

Stable light

Unstable light

Dark

Accessories				
	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm		
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket		
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket		
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm		
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket		
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket		
	REF-C110-2	Reflector, round ø 84 mm, central mounting hole		
	REF-H60-2	Reflector with mounting holes		
	REF-H33	Reflector with screw fixing		
	OFR-70-2	Reflective tape 70 mm x 70 mm		
	REF-H85-2	Reflector, rectangular 84.5 mm x 84.5 mm, mounting holes		
	REF-H50	Reflector, rectangular 51 mm x 61 mm, mounting holes, fixing strap		
	OFR-100/100	Reflective tape 100 mm x 100 mm		
6/	V31-GM-2M-PUR	Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey		
6/	V31-WM-2M-PUR	Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey		