





## Connection cable, Ethernet V1SD-W-70M-PUR-ABG-V1SD-W

- Hard-wearing PUR cable
- Industrial Ethernet
- D coding for Ethernet
- CAT5/CAT5e cable
- Free of paint wetting interfering substances
- Halogen-free
- Screw connection suitable for tool assembly
- Immunity to vibration, with mechanical latching

Ethernet bus cable M12 plug angled to M12 plug angled D-coded, 4-pin, PUR cable blue, Cat5e, shielded



### Dimensions



### Technical Data

#### General specifications

|                   |  |                  |
|-------------------|--|------------------|
| Connector 1       |  |                  |
| Connection        |  | plug             |
| Construction type |  | M12              |
| Style             |  | angled           |
| Locking           |  | screw connection |
| Number of pins    |  | 4                |
| Coding            |  | D-coded          |
| Connector 2       |  |                  |
| Connection        |  | plug             |
| Construction type |  | M12              |
| Style             |  | angled           |
| Locking           |  | screw connection |
| Number of pins    |  | 4                |
| Coding            |  | D-coded          |

#### Electrical specifications

|                   |                |                        |
|-------------------|----------------|------------------------|
| Operating voltage | U <sub>B</sub> | max. 48 V AC / 60 V DC |
| Operating current | I <sub>B</sub> | max. 1 A               |

#### Conformity

|                      |                                     |  |
|----------------------|-------------------------------------|--|
| Degree of protection | EN 60529                            |  |
| Plug connection      | connector M12 x 1 : IEC 61076-2-101 |  |

Release date: 2023-07-12 Date of issue: 2023-07-13 Filename: 70101613\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**

Technical Data

|                           |   |                                                                                |
|---------------------------|---|--------------------------------------------------------------------------------|
| Component category        |   | CAT5 (IEC 11801) , CAT5e (IEC 61156-6)                                         |
| Flammability              |   | IEC 60332-1-2 / UL 2556                                                        |
| Halogen-free              |   | IEC 60754-1                                                                    |
| Ambient conditions        |   |                                                                                |
| Ambient temperature       |   |                                                                                |
| Plug connector            |   | -25 ... 90 °C (-13 ... 194 °F)                                                 |
| Cable, fixed              |   | -40 ... 80 °C (-40 ... 176 °F)                                                 |
| Cable, flexing            |   | -20 ... 80 °C (-4 ... 176 °F)                                                  |
| Pollution degree          |   | 3                                                                              |
| Mechanical specifications |   |                                                                                |
| Plug connector            |   |                                                                                |
| Tightening torque         |   | 0.4 Nm                                                                         |
| Loosening protection      |   | available                                                                      |
| Tool installation         |   | straight knurling                                                              |
| Mating cycles             |   | min. 100                                                                       |
| Shielding                 |   | shield connected to screw connection                                           |
| Degree of protection      |   | IP65/IP67                                                                      |
| Cable                     |   | according to IEC/EN 60228 (DIN VDE 0295) class 5                               |
| Sheath diameter           |   | 6.4 mm                                                                         |
| Bending radius            |   | > 8 x cable diameter, moving<br>> 4 x cable diameter, fixed                    |
| Sheath color              |   | water blue (RAL 5021)                                                          |
| Number of cores           |   | 4                                                                              |
| Core cross section        |   | 0.14 mm²                                                                       |
| Cores color               |   | Core 1: white/orange<br>Core 2: white/green<br>Core 3: orange<br>Core 4: green |
| Core construction         |   | 7 x 0.16 mm Ø<br>twisted pairs                                                 |
| Shield                    |   | aluminum-lined polyester foil<br>Tinned copper braiding, 70 % coverage         |
| Length                    | L | 70 m                                                                           |
| Material                  |   |                                                                                |
| PWIS free                 |   | yes                                                                            |
| Halogen-free              |   | yes                                                                            |
| Plug connector            |   |                                                                                |
| Screw connection          |   | Zinc diecast, nickel-plated                                                    |
| Body                      |   | TPU, black                                                                     |
| Contact surface           |   | Ni/Au                                                                          |
| Flammability              |   | V-2                                                                            |
| Cable                     |   |                                                                                |
| Sheathing                 |   | PUR                                                                            |
| Core insulation           |   | PE                                                                             |
| Flammability              |   | VW-1                                                                           |

Connection



Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Accessories

|                                                                                   |                              |                                                  |
|-----------------------------------------------------------------------------------|------------------------------|--------------------------------------------------|
|  | <b>MH V1-SCREWDRIVER</b>     | Torque screwdriver (0.6 Nm)                      |
|  | <b>MH V1-BIT M12</b>         | plug-in cap M12                                  |
|  | <b>V1/V3-LABELHOLDER</b>     | Label holder                                     |
|  | <b>V1/V3-LABEL</b>           | Label plate                                      |
|  | <b>MH V1-Holder</b>          | Modular universal holder for M12 connectors      |
|  | <b>V1-CLIP</b>               | Unlocking protector for M12 connector            |
|  | <b>V1-MARKING-RING-COLOR</b> | Marking rings for M12 connectors, various colors |