



Model Number


VMBI-2+P/Z2-5M-PUR

Valve connector, Form B (Ind), 2+PE, LED, Z diode, PUR cable

Features

- Z diode as a protective circuit
- Built-in LED, as operating and function indicator
- Moulded seal

Dimensions



Technical data

General specifications

Number of pins	2 + PE
Connection 1	Valve connector industrial version
Construction type 1	right angle
Connection 2	cable end

Indicators/operating means

LED yellow	Functional display
------------	--------------------

Electrical specifications

Operating voltage	U_B	24 V AC/DC
Test voltage		2000 V
Operating current		max. 4 A
Volume resistance		< 10 m Ω

Ambient conditions

Ambient temperature	-25 ... 80 °C (-13 ... 176 °F)
Pollution Degree	3

Mechanical specifications

Protection degree	IP67
Connection	Valve connector Form B (Ind)
Material	
Contacts	CuZn ; CuSn
Body	PUR
Cable	PUR
Core insulation	PVC
Cable	
Sheath diameter	\varnothing 5.7 mm
Bending radius	> 10 x cable diameter, appropriate for conveyor chains
Color	black
Cores	(2 + 1) x 0.5 mm ²
Conductor construction	16 x 0.2 mm \varnothing
Length	L 5 m

Electrical connection

