


HART Termination Board

HiSHPTB/32/FOX2001C-02




- IA 200 replacement FTA
- Designed for FBMs 201, 204, 215 and 237
- 25-pin Sub-D connectors, PCS wiring
- Redundant power supply connections
- Easy to add line impedance



Function

The Termination Board is designed for easy HiDMux2700 Multiplexer integration with Foxboro IA 200 series controller. With the Multiplexer integrated into the board and plug-n-play options for the DCS equipment, this provides a clean and clear access to the HART signals, while reducing the need for marshalling cabinets and extra equipment that reduce cabinet space. The HART Termination Board provides a robust solution for on-line HART communications, interfaces up to 32 field located HART devices, and, it allows the user to replace standard DCS field termination panels.

Connection



Technical Data

Supply	
Rated voltage	U_r 20 ... 30 V DC
Fusing	315 mA , 5 x 20 mm (0.2 x 0.8 inch)
Power dissipation	0.7 W , with Multiplexer
Reverse polarity protection	yes
HART signal channels (intrinsically safe)	
HART signal channels	
Number of channels	32 unbalanced signal loops
Redundancy	
Supply	yes
Galvanic isolation	

Release date: 2023-05-31 Date of issue: 2023-05-31 Filename: 473496_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

HART signal channels	30 V DC
Ambient conditions	
Ambient temperature	0 ... 55 °C (32 ... 131 °F)
Relative humidity	5 ... 90 %, non-condensing
Mechanical specifications	
Core cross section	2.5 mm ² (16 AWG)
Connection	field side: 2 x 37-pin Sub-D socket control side: 4 x 26-pin connectors RS 485 interface: removable screw terminals power: removable screw terminals
Mass	approx. 500 g
Dimensions	260 x 120 x 190 mm (10.2 x 4.7 x 7.5 inch) (W x H x D) , depth including module assembly with HiDMux2700
Mounting	DIN rail mounting
General information	
Supplementary information	Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see www.pepperl-fuchs.com .

Additional Information

Connection Assignment

Terminal block	Channels
LBUG 1	1 ... 8
LBUG 2	9 ... 16
LBUG 3	17 ... 24
LBUG 4	25 ... 32

Configuration

Channel	Switch	Communication resistor shorted (valve)	Communication resistor in series (transmitter)	
1	S1	1	closed	opened
2		2	closed	opened
3		3	closed	opened
4		4	closed	opened
5		5	closed	opened
6		6	closed	opened
7		7	closed	opened
8		8	closed	opened
9	S2	1	closed	opened
10		2	closed	opened
11		3	closed	opened
12		4	closed	opened
13		5	closed	opened
14		6	closed	opened
15		7	closed	opened
16		8	closed	opened
17	S3	1	closed	opened
18		2	closed	opened
19		3	closed	opened
20		4	closed	opened
21		5	closed	opened
22		6	closed	opened
23		7	closed	opened
24		8	closed	opened
25	S4	1	closed	opened
26		2	closed	opened
27		3	closed	opened
28		4	closed	opened
29		5	closed	opened
30		6	closed	opened
31		7	closed	opened
32		8	closed	opened

Foxboro I/O Interfaces

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Additional Information

- for Foxboro module FBM 204 (adapter 509004 required)
- for Foxboro module FBM 201
- for Foxboro module FBM 237
- for Foxboro module FBM 215

Connection via standard Foxboro cable