



Headset

SM1PBWEXP01 ATEX

- SENS® Technology - remain aware of surrounding noises and hazards
- Clear two-way radio communication in high-noise environments
- Compatible with two-way radios and ecom mobile devices via Bluetooth®
- Bluetooth cellular connection for conversation and audio streaming (HFP, HSP and A2DP profiles)
- Improved Short Range with VOX capabilities and additional channel banks for headset-to-headset communications

SM1P, Headband, Zone 1/21, with Bluetooth



Technical Data

General specifications

Description Headband

Hardware

Microphone Boom microphone , noise cancelling

Electrical specifications

Battery type Li-ion , Rechargeable
2250 mAh

Charging time 4 h

Operating duration 18 h

Communication

Bluetooth Bluetooth 3.0
HFP (8 KHz and 16 KHz), HSP, A2DP
Range: 15 m

Connections SENS® 360° Situational Awareness: 95 dB(A)
Half-duplex communications, Up to 8 programmable FM channels, Up to 50 meters

Ambient conditions

Charging temperature 0 ... 40 °C (32 ... 104 °F)

Mechanical specifications

Degree of protection IP54

Mass 495 g

Data for application in connection with hazardous areas

ATEX approval

ATEX certificate Baseefa18ATEX0049X - Issue 1

ATEX marking
 Ⓢ I M2 Ex ib I Mb (-20°C to +60°C)
 Ⓢ II 2G Ex ib IIC T4 Gb (-20°C to +40°C)
 Ⓢ II 2D Ex ib IIC T155°C Db (-20°C to +40°C)

International approvals

IECEx approval

IECEx certificate IECEx BAS 18.0035X

IECEx marking
 Ex ib I Mb (-20°C to +60°C)
 Ex ib IIC T4 Gb (-20°C to +40°C)
 Ex ib IIC T155°C Db (-20°C to +40°C)

Release date: 2020-07-22 Date of issue: 2020-07-22 Filename: 70110932_eng.pdf

Technical Features

Hearing Protection

Volume limiter	82 dB(A) [programmable] - only applicable when the headset is powered on.		
Region	Australia / NZ	USA / Canada	Europe
Standard	AS/NZS 1270	ANSI S3.19	EN352-1/EN352-3
Result	SLC80	NRR	SNR
HB	31 dB, Class 5	27 dB	33 dB
BTN	27 dB, Class 5	24 dB	30 dB
HM	26 dB, Class 5	23 dB	31 dB