



# Pad-Ex® 01 P8 Tablet Computer



## PAD-EX01P8-D2NAMC0508256WIF000

- Capacitive multitouch screen
- 5 MP camera with autofocus and LED flash
- Outstanding wireless connectivity
- Intel Wireless AC9260
- Bluetooth® 5.0
- 11.6 inch widescreen display
- Can be used in sunlight
- Windows® 10 Pro
- 802.11 a/b/g/n/ac
- Eighth-generation Intel® Core™ processor
- Accessories and peripheral devices allow a wider range of applications
- Global certificates - a common platform

Pad-Ex 01 D2 (DIV 2), with camera, i5 processor, 8 GB RAM, 256 GB SSD, Windows 10



### Technical Data

#### Hardware

Processor	Intel Broadwell i5 (8250 U)
Working memory	RAM 8 GByte
Camera	
Front camera	2 MP
Main camera	5 MP Autofocus
Internal data memory	256 GByte
Sensors	Acceleration sensor, gyroscope and e-compass, light sensor

#### Indicators/operating means

Display	Can be operated while wearing gloves
Touchscreen technology	Capacitive multitouch
Type	TFT, LCD
Screen diagonal	29.5 cm (11.6 ")
Aspect ratio	16:9
Resolution	1920x1080 (Full HD)
Brightness	1000 cd/m <sup>2</sup> (nit)
Colors	16 Mio.

#### Electrical specifications

Battery type	Li-Ion battery 43.8 WH 11.1 V 3950 mAh
--------------	--

#### Communication

WLAN	802.11 a/b/g/n/ac (2.4 GHz + 5 GHz)
Bluetooth	Bluetooth® 5.0
GPS sensor	GPS, Glonass, Beidou, Galileo
USB	USB 3.0

#### Software

Operating system	Windows® 10 Pro (64 Bit)
Languages	German, English (default)

#### Ambient conditions

Ambient temperature	-10 ... 55 °C (14 ... 131 °F)
---------------------	-------------------------------

#### Mechanical specifications














Release date: 2022-05-31 Date of issue: 2022-05-31 Filename: 480990-100000\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Technical Data

Degree of protection	IP64
Mass	1200 g
Dimensions	H x W x D 192 mm x 298 mm x 20 mm
<b>International approvals</b>	
SGS approval	
SGS certificate	SGSNA/20/SUW/00020X
Approved for	Class I, II, III, Division 2, GRPS A-G, T4, T135 °C Class I, Zone 2, Group IIC T4
<b>General information</b>	
Scope of delivery	Pad-Ex® AC Adaptor Charging cable Dock Connector with Pass-Through Hand strap Documentation

## Accessories

	<b>VH P01 A01 Vehicle Dock</b>	Vehicle dock for Pad-Ex 01 DZ2, D2
	<b>DS P01 A01 Office Dock</b>	Office docking station for Pad-Ex 01 DZ2 D2
	<b>DC P01 HC Battery charger</b>	Charger for BP P01 HC and BP P01 SC
	<b>CH P01 A01 Shoulder strap</b>	Shoulder strap for Pad-Ex 01 DZ2, D2
	<b>LC P01 A01 Leathercase</b>	Leather case for Pad-Ex 01 DZ2, D2
	<b>HA P01 A01 X-Strap</b>	X-strap for Pad-Ex 01 DZ2, D2
	<b>ST T01 X1i</b>	Stylus pen
	<b>PSPA1C1GE</b>	USB-C to Ethernet Adapter
	<b>CA P01 A01 Hand strap</b>	Hand strap for Pad-Ex 01 DZ2, D2
	<b>PS P01 A01 Power Supply</b>	Power Supply (AC Adapter with AC Power Cord EU) for Pad-Ex® 01 D2, DZ2
	<b>BP_P01_HC_JP</b>	Battery
	<b>BP_P01_SC_JP</b>	Battery
	<b>CC P01 A01 car charger</b>	Car charger for Pad-Ex 01 DZ2 D2

Release date: 2022-05-31 Date of issue: 2022-05-31 Filename: 480990-100000\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0002  
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222  
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
pa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**