




Breakout Box

RocketPort® EXPRESS

ICRPB-16DB25M-S-PM

- RS-232/422/485 software selectable interfaces
- Communication speeds up to 460 Kbps
- 25 KV surge protection

Surge protection and 16 DB-25M connectors




Function

Flexible, reliable and high-speed serial port expansion.

The RocketPort EXPRESS family comprises serial adapter cards compatible with systems supporting x1, x2, x4, x8, x12 or x16 PCI Express expansion slots. Cards are designed for standard and low-profile PCs and servers and ship with a low-profile and a standard-height bracket. All models feature software-selectable RS-232/422/485 serial communication at data transmission speeds up to 921 Kbps. Connection to serial devices are made utilizing RJ45, DB9 or DB25 fan-out cables or DB9 or DB25 interface boxes, depending on the selected model.

Dimensions



Technical Data

General specifications	
UL File Number	E185802
Functional safety related parameters	
MTBF	31.4 a
Electrical specifications	
Surge protection	25 KV / 200 A for 1 ns
Interface	
Interface type	Software selectable interfaces: RS-232 , RS-422 , RS-485
Physical	16 x DB-25
Supported baud rates	300 to 460.8 Kbps
Directive conformity	

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

Electromagnetic compatibility		
Directive 2014/30/EU		EN 61000-4-2:2009 EN 61000-4-3:2006+A1:2008+A2:2010 EN 61000-4-4:2012 EN 61000-4-5:2014+A1:2017 EN 61000-4-6:2014 EN 61000-4-11:2004+A1:2017
RoHS		EN IEC 63000:2018
Standard conformity		
Electrical safety		CSA C22.2 No. 60950 / UL60950
Emitted interference		EN 55032:2015 FCC CFR 47, part 15, subpart B: 2017 ICES-003 AS/NZ5 CISPR 32, FCC Part 15 Subpart B Class A
Noise immunity		EN 55035:2017-07
Ambient conditions		
Ambient temperature		0 ... 60 °C (32 ... 140 °F)
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)
Relative humidity		max. 95 % non-condensing
Altitude		0 ... 3048 m
Mechanical specifications		
Mass		907 g
Dimensions		
Height		22.9 mm
Width		147.3 mm
Length		216 mm
Construction type		Metal housing
Mounting		panel mount

Connection Assignment



Pin	Assignment			
	RS-232	RS-422	RS-485 Full Duplex	RS-485 Half Duplex
1	n.c.	n.c.	n.c.	n.c.
2	TxD	TxD-	TxD-	TRxD-
3	RxD	RxD-	RxD-	n.c.
4	RTS	TxD+	TxD+	TRxD+
5	CTS	RxD+	RxD+	n.c.
6	DSR	n.c.	n.c.	n.c.
7	SIG GND	SIG GND	SIG GND	SIG GND
8	DCD	n.c.	n.c.	n.c.
9 ... 19	n.c.	n.c.	n.c.	n.c.
20	DTR	n.c.	n.c.	n.c.
21	n.c.	n.c.	n.c.	n.c.
22	RI	n.c.	n.c.	n.c.
23 ... 25	n.c.	n.c.	n.c.	n.c.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".