

Features

- Direct PC interface
- 19 inch flat panel monitor
- Panel or rack mount in general-purpose areas
- Touchscreen options
- Antiglare and stainless options

Application


This product is a high-performance industrial flat panel monitor. It is designed as an operator interface device for continuous use in heavy-duty conditions.

It incorporates an industrial grade, high performance active matrix LCD panel, an optional touchscreen, and will connect directly to any DVI, VGA, or NTSC video signal.

It is available in many configurations.



Connection





Supply	
Connection	Two-position screw terminal
Input voltage	+ 12 V DC @ 3.2 A continuous
Indicators/operating means	
Display	
Type	5-wire resistive 5-wire hardened resistive
Screen diagonal	19 inch (483 mm)
Response time	Standard: 12 ms High-bright: 5 ms
Resolution	1280 x 1024 (native mode) , 1024 x 768 , 800 x 600 , 640 x 480
Color depth	24 bit (16.7 M) color supported in any video mode
Contrast	1000:1
Brightness	Standard: 450 cd/m ² (nits) High-bright: 1000 cd/m ² (nits)
Reading angle	160° horizontal , 160° vertical
Life span	back lamp life: 50,000 hrs typical half life (replaceable)
Input devices	15-pin VGA, DVI-I Optional interface to NTSC (camera, live video) via standard BNC connector
Touchscreen	5-wire resistive 5-wire hardened resistive
Interface	
Interface type	RS-232 serial or USB port to host computer via standard cable
Directive conformity	
Electromagnetic compatibility	
Directive 89/336/EEC	EN55022A, EN61000-6-2, EN61000-3-2, EN61000-3-3
Low voltage	
Directive 73/23/EEC	EN60950
Ambient conditions	
Operating temperature	0 ... 50 °C (32 ... 122 °F) ambient, no active cooling devices required
Storage temperature	-10 ... 60 °C (14 ... 140 °F)
Relative humidity	0 ... 90 %, non-condensing
Vibration resistance	5 ... 100 Hz , 1 g, 12 m/s ² , all axes
Impact resistance	30 g, 6 ms, all axes
Mechanical specifications	
Degree of protection	NEMA Type 4/12 (front face and seals). Type 4x with stainless option IP66
Installation	panel or rack mount
Mass	10 kg
Dimensions	Outer bezel: 411 mm x 483 mm (16.2 x 19.0 inch) Rack mount bezel: 399 mm x 483 mm (15.72 x 19.0 inch) Front bezel thickness: 2.5 mm (0.10 inch)
Overall depth	71 mm (2.8 inch) with recessed cable ways
Cut out dimensions	386 mm x 455 mm (15.2 inch x 17.9 inch)
Mounting	VESA 100 mm mounting pattern (peripheral mounting only)
International approvals	
UL approval	E185778

Supplementary information

Statement of Conformity, Declaration of Conformity and instructions have to be observed. For information see www.pepperl-fuchs.com.

Release date 2020-01-21 09:56 Date of issue 2020-01-21 546924_eng.xml

Dimensions



Accessories

- PS100-LC
Power supply
- SCBL*
- Serial touchscreen cable
- UCBL*
- USB touchscreen cable
- VCBL*
- Video cable
- TSP19-5
- Screen protector

Release date 2020-01-21 09:56 Date of issue 2020-01-21 546924_eng.xml

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".


Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0002
pa-info@us.pepperl-fuchs.com

Germany: +49 621 776 2222
pa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
pa-info@sg.pepperl-fuchs.com

Type code



- 19** 19 in (483 mm) monitor
- A0** Non-touch screen with clear glass
Antiglare
- TA** Resistive touch antiglare
- TH** Hardened resistive touch antiglare
- GP** General purpose
- NO** Painted steel, panel mount
- SS** Stainless steel, panel mount
- RM** Rack mount
- NO** No option
- NT** NTSC input
- HB** High-bright display
- NH** High-bright display with NTSC input