


towing bar detection

DG01B-810-18A-5-R1-C3-F07-S15

WITT Sensoric




- Cost-optimized series for standard tasks
- High degree of protection (IP67)
- towing bar detection
- Direct assembly
- Relay output

comfort light grid with towing bar detection





Dimensions

Transmitter



Receiver



Technical Data

General specifications

Effective detection range	1.6 ... 10 m
Threshold detection range	14 m

Release date: 2024-07-01 Date of issue: 2024-07-08 Filename: 64321275_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

Technical Data

Number of protective field beams		18
Light source		IRED
Light type		infrared
Tests		
Marking		CE
Target size		50 mm
Protection field height		810 mm
Opening angle		eff. 5 °
Optical face		frontal
Ambient light limit		100000 Lux
Indicators/operating means		
Operation indicator		Emitter: LED green Receiver: LED green
Function indicator		Emitter: yellow LED Receiver: LED red: lit when the light beam is interrupted LED green: lights up when light beam is free
Stability alarm indicator		available
Electrical specifications		
Operating voltage	U _B	10 ... 30 V DC
Operating current	I _B	Emitter: approx. 30 mA (24 V) receiver: approx. 20 mA (24 V)
Power consumption	P ₀	approx. 1.2 W
Input		
Test input		high active or low active
Output		
Output type		relay
Switching type		light-on
Signal output		100 mA , short-circuit protected , potential-free
Energized/De-energized delay		< 800 ms
Response time		≤ 100 ms
Conformity		
Product standard		EN ISO 13849 , EN 12978 , EN 61000-6-2, EN 61000-6-3
Ambient conditions		
Ambient temperature		-20 ... 60 °C (-4 ... 140 °F)
Storage temperature		-30 ... 70 °C (-22 ... 158 °F)
Relative humidity		max. 95 %, not condensing
Mechanical specifications		
Degree of protection		IP67 according to EN 60529
Connection		fixed cable with M8 plug, 6-pin
Material		
Housing		black anodized aluminum Epoxy resin molded
Mass		approx. 586 g
Dimensions		
Height		930 mm
Width		16 mm
Depth		16 mm

Release date: 2024-07-01 Date of issue: 2024-07-08 Filename: 64321275_eng.pdf