

# Connection cable

## V11-G-BK3,5M-PUR-U-V11-G




- Suitable for drag chains and abrasion resistant
- Suitable for robotic applications / torsion resistant
- Degree of protection IP68 / IP69
- Free of paint wetting interfering substances
- Resistant to microbes and hydrolysis
- UV resistant
- UL listed for USA and Canada
- Halogen-free
- Specific design protects against loosening and inaccurate installation

Cordset M12 socket straight to M12 plug straight A-coded, 3-pin, PUR cable black, UL approved, drag chain suitable, torsion resistant



### Dimensions



### Technical Data

#### General specifications

|                   |  |  |                  |
|-------------------|--|--|------------------|
| Connector 1       |  |  |                  |
| Connection        |  |  | socket           |
| Construction type |  |  | M12              |
| Style             |  |  | straight         |
| Locking           |  |  | screw connection |
| Number of pins    |  |  | 3                |
| Coding            |  |  | A-coded          |
| Connector 2       |  |  |                  |
| Connection        |  |  | plug             |
| Construction type |  |  | M12              |
| Style             |  |  | straight         |
| Locking           |  |  | screw connection |
| Number of pins    |  |  | 3                |
| Coding            |  |  | A-coded          |

#### Electrical specifications

|                   |                |  |                  |
|-------------------|----------------|--|------------------|
| Operating voltage | U <sub>B</sub> |  | max. 250 V AC/DC |
| Operating current | I <sub>B</sub> |  | max. 4 A         |

#### Conformity

|                      |  |  |                                     |
|----------------------|--|--|-------------------------------------|
| Degree of protection |  |  | EN 60529                            |
| Plug connection      |  |  | connector M12 x 1 : IEC 61076-2-101 |
| Flammability         |  |  | UL 1581; DIN EN 60332-2-2           |
| Halogen-free         |  |  | IEC 60754-1                         |

Release date: 2024-02-21 Date of issue: 2024-02-21 Filename: 70128170-100041\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PEPPERL+FUCHS**

## Technical Data

| Approvals and certificates                       |   |  |
|--|---|--|
| UL approval                                      |   | AWM STYLE 20549 AWM I/II A/B 80°C 300V FT2 (cable)           |
| UL File Number                                   |   | E231213  |
| Ambient conditions                               |   |  |
| Ambient temperature                              |   |  |
| Plug connector                                   |   | -40 ... 90 °C (-40 ... 194 °F)                               |
| Cable, fixed                                     |   | -40 ... 80 °C (-40 ... 176 °F)                               |
| Cable, flexing                                   |   | -20 ... 80 °C (-4 ... 176 °F)                                |
| Pollution degree                                 |   | 3  |
| Mechanical specifications                        |   |  |
| Plug connector                                   |   |  |
| Tightening torque                                |   | 0.6 Nm   |
| Loosening protection                             |   | available  |
| Tool installation                                |   | straight knurling and hexagon nut SW = 14 mm                 |
| Mating cycles                                    |   | min. 100   |
| Degree of protection                             |   | IP68 / IP69  |
| Cable  |   |  |
| according to IEC/EN 60228 (DIN VDE 0295) class 6 |   |  |
| Sheath diameter                                  |   | 4.3 mm   |
| Bending radius                                   |   | > 10 x cable diameter, moving<br>> 5 x cable diameter, fixed |
| Sheath stripping force                           |   | max. 80 N / 300 mm   |
| Sheath color                                     |   | black (similar to RAL 9005)                                  |
| Number of cores                                  |   | 3  |
| Core cross section                               |   | 0.34 mm <sup>2</sup>   |
| Cores color                                      |   | Core 1: brown<br>Core 3: blue<br>Core 4: black               |
| Core construction                                |   | 42 x 0.1 mm Ø  |
| Length   | L | 3.5 m  |
| Cable code                                       |   | Li F 9Y 11Y 3 x 0,34   |
| Drag chain suitability                           |   |  |
| Drag chain cycles                                |   | min. 5000000   |
| Motion velocity                                  |   | max. 3.3 m/s   |
| Traverse distance                                |   | max. 5 m   |
| Acceleration                                     |   | max. 5 m/s <sup>2</sup>                                      |
| Torsion cycles                                   |   | min. 1000000   |
| Torsional stress                                 |   | ± 180 °/m  |
| Material   |   |  |
| PWIS free  |   | yes  |
| Halogen-free                                     |   | yes  |
| Plug connector                                   |   |  |
| Screw connection                                 |   | Zinc diecast, nickel-plated                                  |
| Body   |   | TPU, black   |
| Seal   |   | FKM  |
| Contact surface                                  |   | gold plated (Au)   |
| Flammability                                     |   | V-2  |
| Cable  |   |  |
| Sheathing  |   | PUR based on polyether                                       |
| Core insulation                                  |   | PP   |
| UV resistance                                    |   | yes  |
| Chemical resistance                              |   | good   |
| Oil resistance                                   |   | yes  |
| Cooling lubricant resistance                     |   | yes  |
| Microbial resistance                             |   | yes  |

Release date: 2024-02-21 Date of issue: 2024-02-21 Filename: 70128170-100041\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com




Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

 PEPPERL+FUCHS

### Technical Data

|                       |     |
|-----------------------|-----|
| Hydrolysis resistance | yes |
| Flammability          | FT2 |

### Connection



Release date: 2024-02-21 Date of issue: 2024-02-21 Filename: 70128170-100041\_eng.pdf