

Breakout Box

RocketPort® EXPRESS

ICRPB-4DB9M-PM

- RS-232/422/485 software selectable interfaces
- Communication speeds up to 460 Kbps
- 15 KV surge protection
- DB9 male connectors


4 DB-9M connectors



Function

Flexible, reliable and high-speed serial port expansion. The RocketPort EXPRESS family comprises serial adapter cards compatible with systems supporting x1, x2, x4, x8, x12 or x16 PCI Express expansion slots. Cards are designed for standard and low-profile PCs and servers and ship with a low-profile and a standard-height bracket. All models feature software-selectable RS-232/422/485 serial communication at data transmission speeds up to 921 Kbps. Connection to serial devices are made utilizing RJ45, DB9 or DB25 fan-out cables or DB9 or DB25 interface boxes, depending on the selected model.

Dimensions



Technical Data

General specifications

UL File Number E185802

Functional safety related parameters

MTBF 119.1 a

Electrical specifications

Surge protection 15 KV / 200 A for 1 ns

Interface

Interface type Software selectable interfaces: RS-232 , RS-422 , RS-485

Physical 4 x DB9

Supported baud rates 300 to 460.8 Kbps

Directive conformity

Electromagnetic compatibility

Directive 2014/30/EU

EN 61000-4-2:2009
EN 61000-4-3:2006+A1:2008+A2:2010
EN 61000-4-4:2012
EN 61000-4-5:2014+A1:2017
EN 61000-4-6:2014
EN 61000-4-11:2004+A1:2017


RoHS

EN IEC 63000:2018

Technical Data

Standard conformity		
Electromagnetic compatibility		
Electrical safety		CSA C22.2 No. 60950 / UL60950
Emitted interference		EN 55032:2015 FCC CFR 47, part 15, subpart B: 2017 ICES-003 AS/NZ5 CISPR 32, FCC Part 15 Subpart B Class A
Noise immunity		EN 55035:2017-07
Ambient conditions		
Ambient temperature		0 ... 60 °C (32 ... 140 °F)
Storage temperature		-20 ... 85 °C (-4 ... 185 °F)
Relative humidity		max. 95 % non-condensing
Altitude		0 ... 3048 m
Mechanical specifications		
Mass		275 g
Dimensions		
Height		22.9 mm
Width		76.2 mm
Length		139.7 mm
Construction type		Metal housing
Mounting		panel mount

Connection Assignment



Pin	Assignment			
	RS-232	RS-422	RS-485 Full Duplex	RS-485 Half Duplex
1	DCD	n.c.	n.c.	n.c.
2	RxD	RxD-	RxD-	n.c.
3	TxD	TxD-	TxD-	TRxD-
4	DTR	n.c.	n.c.	n.c.
5	SIG GND	SIG GND	SIG GND	SIG GND
6	DSR	n.c.	n.c.	n.c.
7	RTS	TxD+	TxD+	TRxD+
8	CTS	RxD+	RxD+	n.c.
9	RI	n.c.	n.c.	n.c.

Release date: 2025-11-11 Date of issue: 2025-11-11 Filename: 70116472_eng.pdf