

Thru-beam sensor (pair) M100/MV100-IR/76a/103/115b



- Miniature design
- Easy to use
- Full metal thread mounting
- Highly visible LEDs for Power ON and switching state
- Not sensitive to ambient light

Thru-beam sensor, 15 m detection range, infrared light, light/dark on, DC version, PNP output, sensitivity adjuster, emitter switch-off, fixed cable with M12 plug








Function

The optical sensors of this series are suitable for both standard and demanding applications. The series features a miniature housing design, two M3 metal-threaded mounting holes and a highly visible LED status indicator. Each device is equipped with a sensitivity adjuster and a light-on/dark-on changeover switch for increased flexibility. A wide variety of versions are available in both infrared light and red light with PowerBeam for easy alignment. Special versions with BlueBeam are suitable for challenging applications like those in the solar and battery industries.

Dimensions





Technical Data


System components Emitter M100-IR/76a/115b MV100-IR/103/115b Receiver **General specifications** Effective detection range 0 ... 15 m Threshold detection range 20 m Light source **IRED** modulated infrared light Light type Diameter of the light spot approx. 1.5 m at a distance of 20 m Opening angle approx. 2° Optical face frontal Ambient light limit EN 60947-5-2 Functional safety related parameters $MTTF_d$ 860 a 20 a Mission Time (T_M) Diagnostic Coverage (DC) 0 % Indicators/operating means Operation indicator LED green: power on Function indicator Receiver: LED yellow, lights up when light beam is free, flashes when falling short of the operating reserve; OFF when light beam is interrupted Control elements sensitivity adjustment Control elements Light-on/dark-on changeover switch **Electrical specifications** U_{B} 10 ... 30 V DC Operating voltage Ripple max. 10 % No-load supply current I_0 Emitter: ≤ 15 mA Receiver: ≤ 8 mA Input Test input emitter deactivation at +UB Output Switching type The switching type of the sensor is adjustable. The default setting is: light-on Signal output 1 PNP output, short-circuit protected, reverse polarity protected, open collector Switching voltage max. 30 V DC max. 100 mA, resistive load Switching current ≤ 1.5 V DC Voltage drop U_d 250 Hz Switching frequency Response time 2 ms Conformity EN 60947-5-2 Product standard Approvals and certificates cULus Listed, Class 2 Power Source or listed Power Supply with a limited voltage output with (maybe integrated) fuse (max. 3.3 A according UL248), Type 1 enclosure **UL** approval CCC approval CCC approval / marking not required for products rated ≤36 V **Ambient conditions** -30 ... 60 °C (-22 ... 140 °F) Ambient temperature Storage temperature -40 ... 70 °C (-40 ... 158 °F) **Mechanical specifications** Housing width 11 mm 31 mm Housing height 20 mm Housing depth IP67 Degree of protection Connection 300 mm fixed cable with M12 connector, 4-pin Material


Housing

PC (Polycarbonate)

Optical face	РММА
Mass	approx. 40 g (emitter and receiver)
Tightening torque, fastening screws	0.6 Nm
Cable length	0.3 m

Connection






Connection Assignment



Wire colors in accordance with EN 60947-5-2


1	BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)


Assembly



1	Light-Dark-switching	
2	Sensitivity adjuster	
3	Signal display yellow	
4	Operating display green	

Characteristic Curve





Accessories

	OMH-ML100-09	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-S2	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-01	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-02	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-03	Mounting aid for round steel ø 12 mm or sheet 1.5 mm 3 mm
	OMH-ML100-04	Mounting aid for ML100 series, mounting bracket
	OMH-ML100-05	Mounting aid for ML100 series, mounting bracket
*	OMH-F10-ML100	Mounting aid for ML100 series

Accessories

OMH-10 Mounting aid for ML100 series