


Connection cable, Ethernet V19SX-G-GN5M-PUR-E2S-V19X-G

- Hard-wearing PUR cable
- Industrial Ethernet
- UL listed for USA and Canada
- Halogen-free
- Screw connection suitable for tool assembly
- Immunity to vibration, with mechanical latching

Ethernet bus cable M12 plug straight to M12 plug straight X-coded, 8-pin, PUR cable green, Cat6A, pairs shielded and overall shield



Dimensions



Technical Data

General specifications

Connector 1	
Connection	plug
Construction type	M12
Style	straight
Locking	screw connection
Number of pins	8
Coding	X-coded
Connector 2	
Connection	plug
Construction type	M12
Style	straight
Locking	screw connection
Number of pins	8
Coding	X-coded
UL File Number	E520112

Electrical specifications

Operating voltage	U_B	max. 50 V AC / 60 V DC
Operating current	I_B	max. 0.5 A

Conformity

Degree of protection	EN 60529
Fieldbus standard	IEEE 802.3an 10GBASE-T
Plug connection	connector M12 x 1 : IEC 61076-2-109 connector RJ45 : IEC 60603-7

Release date: 2025-02-26 Date of issue: 2025-02-26 Filename: 70117738_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com


PF PEPPERL+FUCHS

Technical Data

Component category	CAT6A (IEC 11801, EN 50173)	
Flammability	IEC 60332-1-2 , UL 1581	
Ambient conditions		
Ambient temperature		
Cable, fixed installation	-40 ... 85 °C (-40 ... 185 °F)	
Cable, flexing	-10 ... 60 °C (14 ... 140 °F)	
Pollution degree	3	
Mechanical specifications		
Plug connector		
Tightening torque	0.6 Nm	
Loosening protection	integrated	
Tool installation	straight knurling , hexagon nut SW = 13 mm	
Mating cycles	min. 100	
Shielding	shield connected to screw connection	
Degree of protection	IP67	
Cable		
Sheath diameter	6.2 mm	
Bending radius	max. 50 mm movable installation max. 25 mm fixed installation	
Sheath color	green (similar to RAL 6018)	
Number of cores	8	
Core cross section	0.14 mm ²	
Cores color	Core 1: white/orange Core 2: orange Core 3: white/green Core 4: green Core 5: white/brown Core 6: brown Core 7: white/blue Core 8: blue	
Core construction	7 x 0.404 mm Ø twisted pairs , twisted pair shield	
Shield	tinned copper braiding twisted pair shield : aluminum-lined polyester foil	
Length	L	5 m
Cable code	Li 02YSC 11Y 4 x 2 x 0,14 (AWG26/7)	
Mass	242.2 g	
Material		
Halogen-free	yes	
Plug connector		
Screw connection	Zinc diecast, nickel-plated	
Body	TPU, black	
Contact surface	Ni/Au	
Flammability	V-2	
Cable		
Sheathing	PUR	
Cores	bare copper (Cu)	
Core insulation	PE	
UV resistance	yes	
Oil resistance	yes	
Flammability	FT1	

Release date: 2025-02-26 Date of issue: 2025-02-26 Filename: 70117738_eng.pdf

Connection Assignment



Release date: 2025-02-26 Date of issue: 2025-02-26 Filename: 70117738_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**