



## Countersunk profile rail PGV-PR-GM-START

Sturdy construction

Countersunk rail for starting continuous tracks

## **Dimensions**





## **Technical Data**

Release date: 2022-07-04 Date of issue: 2022-07-04 Filename: 70132445\_eng.pdf

General specifications	
Length	65.1 mm
Width	60 mm
Ambient conditions	
Operating temperature	-40 80 °C (-40 176 °F)
Installation temperature	10 40 °C (50 104 °F)
Mechanical specifications	
Material thickness	4 mm
Material	AIMg4.5Mn0.7
Surface	ELOX-E0EV1-15

Mass 24 g

## Mounting

Countersunk profile rails are embedded into a pre-milled groove in the floor. These are glued or screwed into the floor groove depending on the application. The milled floor groove is then grouted with suitable filler material. The groove for the countersunk profile rails must be protected against penetration of glue or filler material during installation. Once the filler material has dried out, the corresponding metal code bar is inserted into the countersunk profile rails via the self-adhesive rear side. If necessary, metal code bars that have been glued in can be replaced by levering them out.