


Inductive sensor


NJ5-11-N-G-Y317937



■ 5 mm non-flush



Dimensions



Technical Data

General specifications			
Switching function			Normally closed (NC)
Output type			NAMUR
Rated operating distance	s_n		5 mm
Installation			non-flush
Assured operating distance	s_a		0 ... 4.05 mm
Reduction factor r_{Al}			0.4
Reduction factor r_{Cu}			0.3
Reduction factor r_{304}			0.85
Output type			2-wire
Nominal ratings			
Nominal voltage	U_o		8.2 V (R_i approx. 1 k Ω)
Switching frequency	f		0 ... 3000 Hz
Hysteresis	H		typ. 5 %
Suitable for 2:1 technology			yes , Reverse polarity protection diode not required
Current consumption			
Measuring plate not detected			min. 3 mA

Release date: 2024-05-27 Date of issue: 2024-05-29 Filename: 70133023_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 PEPPERL+FUCHS

Technical Data

Measuring plate detected	≤ 1 mA
Functional safety related parameters	
MTTF _d	11774 a
Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %
Compliance with standards and directives	
Standard conformity	
NAMUR	EN 60947-5-6:2000 IEC 60947-5-6:1999
Standards	EN IEC 60947-5-2
Approvals and certificates	
IECEX approval	
Equipment protection level Gb	IECEX PTB 11.0037X
Equipment protection level Da	IECEX PTB 11.0037X
Equipment protection level Mb	IECEX PTB 11.0037X
ATEX approval	
Equipment protection level Gb	PTB 00 ATEX 2048 X
Equipment protection level Da	PTB 00 ATEX 2048 X
UL approval	cULus Listed, General Purpose
CCC approval	
Hazardous Location	2020322315002255
NEPSI approval	
NEPSI certificate	GYJ16.1393X
CML approval	on request
ANZEx	18.3018X
Ambient conditions	
Ambient temperature	-25 ... 100 °C (-13 ... 212 °F)
Mechanical specifications	
Connection type	cable
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	PVDF
Degree of protection	IP68
Cable	
Cable diameter	4.8 mm ± 0.2 mm
Bending radius	> 10 x cable diameter
Material	PUR
Core cross section	0.34 mm ²
Length	L 2 m
Dimensions	
Length	31 mm
Diameter	14 mm
General information	
Use in the hazardous area	see instruction manuals

Connection

