

Metal code bar

PXV000003M-AAMH50x100-000003


- High temperature resistance
- High mechanical stability
- Easily exchangeable
- Chemically highly resistant
- 2-colored Data Matrix codes

DataMatrix metal code bars for positioning safePXV and safePGV read heads

Function

Rugged Data Matrix metal code bars made of anodized aluminum for use on the ground in camera-based track guidance. Depending on the application, the code bars can be glued directly to the floor, or glued into special carrier profile rails. The code bars are available in modular lengths of 100, 200, and 500 mm.

Dimensions



Technical Data

General specifications	
Total length	3 m
Start position	3 m
Code bar segment	
Length	100 mm
Width	50 mm
Ambient conditions	
Operating temperature	-40 ... 80 °C (-40 ... 176 °F)
Installation temperature	10 ... 40 °C (50 ... 104 °F)
Environmental resistance	UV radiation Humidity
Chemical resistance	Oils Grease Fuels Aliphatic solvents Weak acids
Mechanical specifications	
Material thickness	1 mm
Material	Aluminum
Mounting type	screwing
Mass	83 g / m
Manufacturing tolerance	± 1 mm/m

Release date: 2023-07-24 Date of issue: 2023-07-24 Filename: 70127564-100061_..._eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PF PEPPERL+FUCHS

Mounting

Mounting Instructions for Adhesive Mounting Type

Preparing the Base Surface

1. Use clean cleaning cloths (free from lint and plasticizers) to clean the surfaces.
2. Use cleaning agents appropriate for the level of surface contamination, for example n-Heptane, ethanol, or a 50:50 mixture of isopropanol and water.
3. Clean the surface until it is completely dry and free of dust, oil, oxides, release agents, and other contaminants.
4. Ensure that the surface is dry, clean, and stable.

Adhesive Strength

Metal	Material with high-energy surfaces	Material with low-energy surfaces
33 N/25 mm	32 N/25 mm	31 N/25 mm

Material thickness: 1 mm code bar + 0.13 mm adhesive

Processing Instructions

During bonding, the pressure should be as high as possible, and the temperature should be at least +10 °C. The higher the pressure and temperature, the better the adhesive will penetrate the pores of the base surface. This allows higher adhesive strength values to be achieved. After about 72 hours, the adhesive is cured.

Type Code

Structure of the type code

P	X	V	(1)	(1)	(1)	(1)	(1)	(1)	M	-	A	A	M	(2)	(3)	(3)	x	(4)	(4)	(4)	-	(5)	(5)	(5)	(5)	(5)	(5)
----------	----------	----------	-----	-----	-----	-----	-----	-----	----------	---	----------	----------	----------	-----	-----	-----	----------	-----	-----	-----	---	-----	-----	-----	-----	-----	-----

PGV	Sensor Type
PXV	Position Extended Vision

(1) (1) (1) (1) (1) (1)	Total length of the code bar
1 ... 100,000	The total length of the code bar is determined by the number of individual code bar segments. The code bars can be ordered in 1 m units.

M	Unit
M	Length in meters

AAM	Code Bar
A	Code bar
A	Absolute code bar
M	Metal code bar




(2)	Mounting Type
G	Mounted by bonding with the adhesive applied to the back. Bonded directly on the floor or in special profile rails.
H	Mounted by screwing or riveting to the support material.

(3) (3)	Code Bar Width
30	Width of the code bar in mm for mounting by bonding.
50	Width of the code bar in mm for mounting by screwing or riveting.

(4) (4) (4)	Code Bar Length
100	Length of the individual code bars in mm.
200	Length of the individual code bars in mm.
500	Length of the individual code bars in mm.















(5) (5) (5) (5) (5) (5)	Start position
1 ... 99,999	Start position of the code bars in m.

Accessories

	PGV-PR-GM-CLOSE100	Countersunk rail for mounting in a floor groove
	PGV-PR-GM-CLOSE200	Countersunk rail for mounting in a floor groove
	PGV-PR-GM-CLOSE500	Countersunk rail for mounting in a floor groove

Release date: 2023-07-24 Date of issue: 2023-07-24 Filename: 70127564-100061_eng.pdf

Accessories

	PGV-PR-GM-CONT100	Countersunk rail for realization of continuous tracks
	PGV-PR-GM-CONT200	Countersunk rail for realization of continuous tracks
	PGV-PR-GM-CONT500	Countersunk rail for realization of continuous tracks
	PGV-PR-GM-END	Countersunk rail to end continuous tracks
	PGV-PR-GM-START	Countersunk rail for starting continuous tracks
	PGV-PR-SM-CLOSE100	Drive-over rail to mounting on the floor
	PGV-PR-SM-CLOSE200	Drive-over rail to mounting on the floor
	PGV-PR-SM-CLOSE500	Drive-over rail to mounting on the floor
	PGV-PR-SM-CONT100	Drive-over rail to realize endless tracks
	PGV-PR-SM-CONT200	Drive-over rail to realize endless tracks
	PGV-PR-SM-CONT500	Drive-over rail to realize endless tracks
	PGV-PR-SM-END	Drive-over rail to end continuous tracks
	PGV-PR-SM-START	Drive-over rail for starting continuous tracks
	PGV-MG30-START-END-SET	Opening segment and closing segment (kit)

Release date: 2023-07-24 Date of issue: 2023-07-24 Filename: 70127564-100061_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

 **PEPPERL+FUCHS**