



Drive-over rail to realize endless tracks

Dimensions





Technical Data

General specifications				
Length	135.5 mm			
Width	60 mm			
Ambient conditions				
Operating temperature	-40 80 °C (-40 176 °F)			
Installation temperature	10 40 °C (50 104 °F)			
Mechanical specifications				
Material thickness	4 mm			
Material	AIMg4.5Mn0.7			
Surface	ELOX-E0EV1-15			

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Pepperl+Fuchs Group www.pepperl-fuchs.com USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



Technical Data

Mass

41 g

Mounting

Drive-over profile rails are screwed directly to the floor. Alternatively, the drive-over profile rails can be glued to the subfloor. The corresponding metal code bar is then inserted into the drive-over profile rails via the self-adhesive rear side. If necessary, metal code bars that have been glued in can be replaced by levering them out.

Accessories

AST -	PGV-PR-SM-END	Drive-over rail to end continuous tracks
~ ??	PGV-PR-SM-START	Drive-over rail for starting continuous tracks

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

2