

# Head lamp

## Lite-Ex PL 10e H 25°



- Ex-zone 0/20
- Ring switch
- High performance LED
- 64 lumen
- Rugged housing
- Diaphragm valve for pressure compensation
- Extremely lightweight
- Durable headband

Explosion-protected LED head lamp with 25° tilt angle (ATEX / IECEx zone 0/20)



### Technical Data

#### General specifications

Bulb	High performance LED
Luminous intensity	1800 Lux (1 m distance)
Luminous flux	64 lumen

#### Electrical specifications

Battery type	3x LR03 / AAA (type-tested)
Operating duration	approx. 55 h (continuous operation)

#### Approvals and certificates

CE conformity	CE 0102
---------------	---------

#### Ambient conditions

Ambient temperature	-20 ... 50 °C (-4 ... 122 °F)
Storage temperature	-30 ... 60 °C (-22 ... 140 °F) (without batteries)

#### Mechanical specifications

Degree of protection	IP 65 IP 67 following EN/IEC 60529 (industrial standard)
Mass	approx. 180 g (with head band)
Dimensions	60 mm x 87 mm x 69 mm

#### Data for application in connection with hazardous areas

EU-type examination certificate	EPS 16 ATEX 1 170 X
Marking	Ⓜ II 1G Ex ia IIC T4 Ga IP65 Ⓜ II 1D Ex ia IIIC T130°C Da IP65

#### International approvals

IECEx approval	
IECEx certificate	IECEx EPS 16.0074X
IECEx marking	Ex ia IIC T4 Ga IP65 Ex ia IIIC T130°C Da IP65

#### General information

Scope of delivery	Lite-Ex® PL 10e H Batteries Headband Documentation
-------------------	---

Release date: 2023-01-16 Date of issue: 2023-01-16 Filename: 70138466\_eng.pdf