Release date: 2023-10-25 Date of issue: 2023-10-25 Filename: 70141166-100008_eng.pdf

Vibration sensor

VIM62PP-E1V16-0HE-I420V14

- Extended temperature range
- Screw-in thread for simple installation
- Simple electrical commissioning
- Rugged stainless steel housing
- Vibration velocity in mm/s via root mean square formation (rms)
- Suitable for use in harzadous area for Class I/II and Division 2

Vibration sensor with analog current output, increased temperature resistance, suitable for Class I/II and Division 2







Function

The vibration sensor determines the vibration quantity using rms (root meas square) averaging. This form of quadratic averaging or pre-filtering enables precise trend statements about the condition of the application.


Furthermore, the vibration sensor has an additional output for the output of the measured temperature value.

The sensor's design is impressively robust against tough environmental conditions.

The stainless steel housing provides optimal protection against corrosion. The wide temperature range of the sensor enables reliable measured values even in harsh conditions.

The simple mounting allows for commissioning in any application.

Dimensions




Technical Data

General specifications	
Туре	Vibration sensor
Measuring technology	MEMS

Technical Data Series Performance Plus Line Vibration velocity Measured variable Measurement range Vibration velocity 0 ... 16 mm/s rms $\pm\,0.1\,$ mm/s (calibration point: 90% of the measuring range; 159.2 Hz) Complies with the tolerance requirements of DIN ISO 2954 for measurement range Measurement accuracy greater than 8 mm/s Cross-sensitivity < 5 % of the partial lateral acceleration, which acts exactly 90° to the measuring axis 10 ... 1000 Hz Frequency range for v-rms: 2 s Averaging time **Electrical specifications** Fusing external fuse is required: 3 A, semi-time-lag, 30 V DC 10 ... 30 V DC Operating voltage U_B max 25 mA Current consumption Power consumption P_0 max. 750 mW Time delay before availability 10 s (rms filter is calculated intially with measurement data before they are available at t_v the output) up to 2 kV Surge protection Output 1 Output type analog output, current output of the vibration variable 4 ... 20 mA Output current Load resistor ≤ 500 Ω Standard conformity Degree of protection DIN EN 60529, IP66, IP67 Shock resistance DIN EN 60068-2-27, 60 g, 6 ms Vibration resistance DIN EN 60068-2-6, 16.5 g, 10 ... 1000 Hz Approvals and certificates **UL** approval E468231 cULus Listed, Class III Power Source and limited energy, if UL marking is **Ordinary Location** marked on the product. For use in NFPA 70 Applications only. adapters providing field wiring on request Hazardous Location F106378 Maximum permissible ambient temperature max. 60 °C (max. 140 °F) Control drawing 116-0492 **Ambient conditions** Ambient temperature -40 ... 60 °C (-40 ... 140 °F) Measuring head temperature -40 ... 125 °C (-40 ... 257 °F) directly at the mounting point Storage temperature -40 ... 60 °C (-40 ... 140 °F) Mechanical specifications Connection type plug Housing material Stainless steel 1.4305 / AISI 303 Housing length 82.35 mm Housing diameter 31 mm Degree of protection IP66 / IP67 only in connected state Connector Threading M12 Number of pins 4 Mass approx. 200 g General information Use in the hazardous area see instruction manuals Only use accessories specified by the manufacturer.

EPPPERL+FUCHS

Connection



Connection Assignment



Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.

Installation

Further Documentation

The sensor manual is also available as detailed overall documentation. Among other things, installation, grounding concepts and mounting are described there in detail.
You can access the manual via the product detail page at www.pepperl-fuchs.com.

The correct electrical connection and the selection of the appropriate grounding concept are crucial for malfunction-free operation of the sensor. For detailed information you may refer to the manual of the sensor.

fa-info@us.pepperl-fuchs.com