

Vibration sensor with analog current output, increased temperature resistance, suitable up to Zone 1/21 with type of protection explosionproof enclosure



#### **Function**


The vibration sensor determines the vibration quantity using rms (root meas square) averaging. This form of quadratic averaging or pre-filtering enables precise trend statements about the condition of the application.

The sensor's design is impressively robust against tough environmental conditions.

The stainless steel housing provides optimal protection against corrosion. The wide temperature range of the sensor enables reliable measured values even in harsh conditions. Furthermore there is an approval for the use of the sensor in hazardous areas.

The simple mounting allows for commissioning in any application.

## Dimensions



# **Technical Data**

#### **General specifications**

Type Measuring technology

Vibration sensor

MEMS


Refer to "General Notes Relating to Pepperl+Fuchs Product Information"



| Technical Data                 |                |   |
|--------------------------------|----------------|---|
| Series                         |                | Performance Plus Line   |
| Measured variable              |                | Vibration velocity  |
| Measurement range              |                | violation volodity  |
| Vibration velocity             | V-             | 032 mm/s  |
| Vibration volocity             | rms            |   |
| Measurement accuracy           |                | ± 0.1 mm/s (calibration point: 90% of the measuring range; 159.2 Hz)<br>Complies with the tolerance requirements of DIN ISO 2954 for measurement range<br>greater than 8 mm/s |
| Cross-sensitivity              |                | $< 5~\%$ of the partial lateral acceleration, which acts exactly $90^\circ$ to the measuring axis   |
| Frequency range                |                | 10 1000 Hz  |
| Averaging time                 |                | for v-rms: 2 s  |
| Electrical specifications      |                |   |
| Fusing                         |                | external fuse is required: 3 A , semi-time-lag , 30 V DC  |
| Operating voltage              | U <sub>B</sub> | 10 30 V DC  |
| Current consumption            |                | max. 25 mA  |
| Power consumption              | P <sub>0</sub> | max. 750 mW   |
| Time delay before availability | t <sub>v</sub> | 10 s (rms filter is calculated intially with measurement data before they are available at the output)  |
| Surge protection               |                | up to 2 kV  |
| Output 1                       |                |   |
| Output type                    |                | analog output, current<br>output of the vibration variable  |
| Output current                 |                | 4 20 mA   |
| Load resistor                  |                | $\leq 500 \ \Omega$   |
| Standard conformity            |                |   |
| Degree of protection           |                | DIN EN 60529, IP66, IP67  |
| Shock resistance               |                | DIN EN 60068-2-27, 60 g, 6 ms   |
| Vibration resistance           |                | DIN EN 60068-2-6, 16.5 g, 10 1000 Hz  |
| Approvals and certificates     |                |   |
| IECEx approval                 |                |   |
| Equipment protection level Gb  |                | IECEx CSAE 22.0042X   |
| Equipment protection level Db  |                | IECEx CSAE 22.0042X   |
| ATEX approval                  |                |   |
| Equipment protection level Gb  |                | CSANe 21 ATEX 1074 X  |
| Equipment protection level Db  |                | CSANe 21 ATEX 1074 X  |
| Ambient conditions             |                |   |
| Ambient temperature            |                | -40 60 °C (-40 140 °F)  |
| Measuring head temperature     |                | -40 125 °C (-40 257 °F) directly at the mounting point  |
| Storage temperature            |                | -40 60 °C (-40 140 °F)  |
| Mechanical specifications      |                |   |
| Connection type                |                | cable   |
| Housing material               |                | Stainless steel 1.4305 / AISI 303   |
| Housing length                 |                | 82.35 mm  |
| Housing diameter               |                | 31 mm   |
| Degree of protection           |                | IP66 / IP67 only in connected state   |
| Cable                          |                |   |
| Number of cores                |                | 4   |
| Core cross section             |                | 0.34 mm <sup>2</sup>  |
| Length                         | L              | 5 m   |
| Tension force                  |                | max. 80 N (tensile loading directly at the cable, not at the metal conduit if attached)   |
| Mass                           |                | 460 g   |
| General information            |                |   |
| Use in the hazardous area      |                | see instruction manuals<br>Only use accessories specified by the manufacturer.  |
|                                |                |   |

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

### Connection



## Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.

#### Installation

#### **Further Documentation**

The sensor manual is also available as detailed overall documentation. Among other things, installation, grounding concepts and mounting are described there in detail.

You can access the manual via the product detail page at www.pepperl-fuchs.com.

#### Note

The correct electrical connection and the selection of the appropriate grounding concept are crucial for malfunction-free operation of the sensor. For detailed information you may refer to the manual of the sensor.

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

3