



- 45° cable outlet for maximum mounting freedom under extremely
- Extremely small light spot for very high switching point accuracy
- Precision object detection, almost irrespective of the color


Triangulation sensor with background suppression for standard applications, miniature design, 15 mm detection range, red light, light on, NPN output, 200 mm fixed cable with plug M8, 4-pin



#### **Function**

The nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options.

### **Dimensions**



### **Technical Data**

| General specifications |                                      |
|------------------------|--------------------------------------|
| Detection range        | 2 15 mm                              |
| Reference target       | standard white, 100 mm x 100 mm      |
| Light source           | LED                                  |
| Light type             | modulated visible red light , 630 nm |

USA: +1 330 486 0001 fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111 fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091 fa-info@sg.pepperl-fuchs.com



# **Technical Data**

| Technical Data                       |                |  |
|--------------------------------------|----------------|--|
| Black-white difference (6 %/90 %)    |                | < 5 % at 15 mm   |
| Angle deviation                      |                | approx. 2 °  |
| Diameter of the light spot           |                | approx. 2 mm at a distance of 15 mm  |
| Opening angle                        |                | approx. 2 °  |
| Optical face                         |                | frontal  |
| Ambient light limit                  |                | EN 60947-5-2 : 30000 Lux   |
| Functional safety related parameters |                |  |
| MTTF <sub>d</sub>                    |                | 800 a  |
| Mission Time (T <sub>M</sub> )       |                | 20 a   |
| Diagnostic Coverage (DC)             |                | 0 %  |
| Indicators/operating means           |                |  |
| Operation indicator                  |                | LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 Hz) |
| Function indicator                   |                | LED yellow ON: lights when object is detected  |
| Electrical specifications            |                |  |
| Operating voltage                    | U <sub>B</sub> | 10 30 V DC , class 2   |
| No-load supply current               | I <sub>0</sub> | < 10 mA  |
| Output                               | -              |  |
| Switching type                       |                | NO contact / light on  |
| Signal output                        |                | 1 NPN output, short-circuit protected, reverse polarity protected, open collector      |
| Switching voltage                    |                | max. 30 V DC   |
| Switching current                    |                | max. 50 mA, resistive load   |
| Voltage drop                         | U <sub>d</sub> | ≤ 1.5 V DC   |
| Switching frequency                  | f              | approx. 800 Hz   |
| Response time                        |                | 600 μs   |
| Conformity                           |                | ·  |
| Product standard                     |                | EN 60947-5-2   |
| Approvals and certificates           |                |  |
| UL approval                          |                | cULus Recognized, Class 2 Power Source   |
| CCC approval                         |                | CCC approval / marking not required for products rated $\leq$ 36 V                     |
| Ambient conditions                   |                |  |
| Ambient temperature                  |                | -25 60 °C (-13 140 °F)   |
| Storage temperature                  |                | -30 70 °C (-22 158 °F)   |
| Mechanical specifications            |                |  |
| Housing width                        |                | 7.5 mm   |
| Housing height                       |                | 26 mm  |
| Housing depth                        |                | 13.8 mm  |
| Degree of protection                 |                | IP67   |
| Connection                           |                | 200 mm fixed cable with 4-pin, M8x1 connector  |
| Material                             |                | ·  |
| Housing                              |                | PC/ABS and TPU   |
| Optical face                         |                | PC   |
| Cable                                |                | PUR  |
| Mass                                 |                | approx. 20 g   |
|                                      |                |  |


 Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

 Pepperl+Fuchs Group
 USA: +1 330 486 0001
 Gr

 www.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com
 fa-info@us.pepperl-fuchs.com

2

### Connection




# **Connection Assignment**



Wire colors in accordance with EN 60947-5-2


| 1 | BN | (brown) |
|---|----|---------|
| 2 | WH | (white) |
| 3 | BU | (blue)  |
| 4 | BK | (black) |

# Assembly



| 1 | Operating display | green  |
|---|-------------------|--------|
| 2 | Signal display    | yellow |
| 3 | Emitter           |        |
| 4 | Receiver          |        |

#### **Characteristic Curve**




Release date: 2023-09-06 Date of issue: 2023-09-06 Filename: 70141855\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

USA: +1 330 486 0001 G fa-info@us.pepperl-fuchs.com fa

3

### **Characteristic Curve**



### Accessories

| 000 HI | MH-R3-01      | Mounting aid for sensors from the R3 series, mounting bracket          |
|--------|---------------|--|
| ,      | MH-R3-02      | Mounting aid for sensors from the R3 series, mounting bracket          |
| 00011  | MH-R3-03      | Mounting aid for sensors from the R3 series, mounting bracket          |
| ,      | MH-R3-04      | Mounting aid for sensors from the R3 series, mounting bracket          |
| ø /    | V31-GM-2M-PUR | Female cordset single-ended M8 straight A-coded, 4-pin, PUR cable grey |
| 6/     | V31-WM-2M-PUR | Female cordset single-ended M8 angled A-coded, 4-pin, PUR cable grey   |

4