

Triangulation sensor (BGS) OBT50-R3-E0-P-L



- Ultra-small housing design
- DuraBeam Laser Sensors durable and employable like an LED
- 45° cable outlet for maximum mounting freedom under extremely tight space constraints
- Precision object detection, almost irrespective of the color


Laser triangulation sensor with background suppression, ultra-small design with M3 mounting, 50 mm sensing range, light on, NPN output, 2 m fixed cable



Function

The R3 series nano sensor has been developed for a broad range of applications. It offers excellent durability and is exceptionally easy to install. The housing is compact and, with its 45° cable outlet, can be installed in the smallest spaces. New functional principles and functionality open up a range of new options. The DuraBeam laser sensors are durable and can be used in the same way as a standard sensor.

Dimensions



Technical Data

General specifications	
Detection range	7 50 mm
Reference target	standard white, 100 mm x 100 mm
Light source	laser diode
Light type	modulated visible red light , 680 nm




Technical Data

Lacor nominal ratings			
Laser nominal ratings Note		LACED LIGHT DO NOT STADE INTO DEAM	
		LASER LIGHT, DO NOT STARE INTO BEAM	
Laser class		1	
Wave length		680 nm	
Beam divergence		> 5 mrad	
Pulse length		approx. 3 µs	
Repetition rate		approx. 16.6 kHz	
max. pulse energy		9.5 nJ	
Black-white difference (6 %/90 %)		< 10 % at 50 mm	
Diameter of the light spot		approx. 0.8 mm at a distance of 50 mm	
Opening angle		approx. 2 ° frontal	
Optical face			
Ambient light limit		EN 60947-5-2 : 30000 Lux	
Functional safety related parameters		900 a	
$MTTF_d$ $MissionTime(T_M)$		800 a	
(,		20 a	
Diagnostic Coverage (DC)		0 %	
Indicators/operating means		LED groop statically lit Power on short sirevity LED groop fleeking (approx. 4.1.1-)	
Operation indicator Function indicator		LED green, statically lit Power on , short-circuit : LED green flashing (approx. 4 Hz)	
		LED yellow: lights when object is detected	
Electrical specifications		10 041/	
Operating voltage	U _B	12 24 V	
No-load supply current Protection class	I ₀	< 10 mA	
		III	
Output Cuitabing type		NO contest / light on	
Switching type		NO contact / light-on	
Signal output		1 NPN output, short-circuit protected, reverse polarity protected, open collector max. 30 V DC	
Switching voltage			
Switching current Voltage drop	U _d	max. 50 mA , resistive load ≤ 1.5 V DC	
• .	f		
Switching frequency Response time	'	approx. 2 kHz 250 μs	
Conformity		250 μs	
Product standard		EN 60947-5-2	
Standard conformity		EN 00947-3-2	
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 EN 60825-1:2007 UL 60947-5-2: 2014	
Approvals and certificates		LN 00347-3-2.2007 LN 00347-3-2/A1.2012 LN 00023-1.2007 OL 00347-3-2. 2014	
UL approval		E87056, cULus Recognized, Class 2 Power Source	
CCC approval		CCC approval / marking not required for products rated ≤36 V	
FDA approval		IEC 60825-1:2007 Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007	
Ambient conditions			
Ambient temperature		-20 60 °C (-4 140 °F)	
Storage temperature		-30 70 °C (-22 158 °F)	
Mechanical specifications			
Housing width		7.5 mm	
Housing height		26 mm	
Housing depth		13.8 mm	
Degree of protection		IP67	
o ::		2 m fixed cable	
Connection			
Material			
		PC/ABS and TPU	


Technical Data

Cable	PUR
Mass	approx. 20 g
Cable length	2 m

Connection Assignment




Assembly



1	Operating display	green
2	Signal display	yellow
3	Emitter	
4	Receiver	

Characteristic Curve



Safety Information



CLASS 1 LASER PRODUCT IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

CLASS 1 LASER PRODUCT

IEC 60825-1: 2007 certified. Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No. 50, dated June 24, 2007

Safety Information

Laser Class 1 Information

The irradiation can lead to irritation especially in a dark environment. Do not point at people! Maintenance and repairs should only be carried out by authorized service personnel!

Attach the device so that the warning is clearly visible and readable.

The warning accompanies the device and should be attached in immediate proximity to the device.

Caution – Use of controls or adjustments or performance of procedures other than those specified herein may result in hazardous radiation exposure.

Accessories



Release date: 2023-09-06 Date of issue: 2023-09-06 Filename: 70141907_eng.pdf

MH-R3-01

Mounting aid for sensors from the R3 series, mounting bracket

MH-R3-02

Mounting aid for sensors from the R3 series, mounting bracket



Refer to "General Notes Relating to Pepperl+Fuchs Product Information"

Accessories MH-R3-03 Mounting aid for sensors from the R3 series, mounting bracket MH-R3-04 Mounting aid for sensors from the R3 series, mounting bracket