


# Inductive sensor


## NCB1,5-8GM25-N0-Y306375



■ 1.5 mm flush



### Dimensions



### Technical Data

General specifications			
Output type			NAMUR
Rated operating distance	$s_n$		1.5 mm
Installation			flush
Assured operating distance	$s_a$		0 ... 1.215 mm
Actual operating distance	$s_r$		1.35 ... 1.65 mm typ.
Reduction factor $r_{Al}$			0.3
Reduction factor $r_{Cu}$			0.2
Reduction factor $r_{304}$			0.7
Output type			2-wire
Nominal ratings			
Nominal voltage	$U_o$		8.2 V ( $R_i$ approx. 1 k $\Omega$ )
Switching frequency	$f$		0 ... 2000 Hz
Hysteresis	$H$		1 ... 10 typ. 3 %
Reverse polarity protection			reverse polarity protected
Short-circuit protection			yes
Suitable for 2:1 technology			yes , Reverse polarity protection diode not required

Release date: 2023-09-06 Date of issue: 2023-09-06 Filename: 70133335\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com

Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS

## Technical Data

<b>Current consumption</b>		
Measuring plate not detected		min. 3 mA
Measuring plate detected		≤ 1 mA
<b>Functional safety related parameters</b>		
MTTF <sub>d</sub>		3590 a
Mission Time (T <sub>M</sub> )		20 a
Diagnostic Coverage (DC)		0 %
<b>Compliance with standards and directives</b>		
Standard conformity		
NAMUR		EN 60947-5-6:2000 IEC 60947-5-6:1999
Standards		EN 60947-5-2:2007 EN 60947-5-2/A1:2012 IEC 60947-5-2:2007 IEC 60947-5-2 AMD 1:2012
<b>Approvals and certificates</b>		
CCC approval		CCC approval / marking not required for products rated ≤36 V
<b>Ambient conditions</b>		
Ambient temperature		-25 ... 100 °C (-13 ... 212 °F)
Storage temperature		-40 ... 100 °C (-40 ... 212 °F)
<b>Mechanical specifications</b>		
Connection type		cable
Connection assembly		Protective hose : stainless steel 1.4301 / AISI 304 screwed connection : MS58 nickel-plated
Housing material		Stainless steel 1.4305 / AISI 303
Sensing face		LCP
Degree of protection		IP67
Cable		
Bending radius		> 10 x cable diameter
Material		PVC
Core cross section		0.14 mm <sup>2</sup>
Length	L	2 m
Cable protection		Protective hose 60 cm
<b>General information</b>		
Use in the hazardous area		see instruction manuals

## Connection

