

# USB supply cable for corded IDM-Z2-\*

## SK-IDM-Z2-J2-1M-U-N



- Cable-Barrier for corded 1-D and 2-D reader and base station
- Enable operation in Zone 2/22
- USB Ex ic (via M12 female socket) connection

Cable barrier for corded IDM-Z2-\* handheld readers and base station



### Function

SK-IDM-Z2-\* cable barriers provide intrinsically safe power to IDM-Z2-\* 1-D and 2-D handheld readers, as well as IDM-Z2-x6x-B-J2\* Bluetooth® base and charging stations. SK-IDM-Z2-\* supply modules enable operation of handheld scanners in Zone 2/22.

### Technical Data

General specifications	
Type	Cable barrier
Supply	
Power consumption	DC +5 V ±10 %
Electrical specifications	
Current consumption	1 A
Interface	
Interface type	field side : USB via the USB port of the host PC Connection side handheld readers and base station : USB Ex ic (via M12 female socket)
Directive conformity	
Electromagnetic compatibility	
Directive 2014/30/EU	EN 61000-6-2:2005 + AC:2005 , EN 61000-6-4:2007 + A1:2011
Ambient conditions	
Operating temperature	-20 ... 70 °C (-4 ... 158 °F)
Storage temperature	-20 ... 70 °C (-4 ... 158 °F)
Relative humidity	95 % non-condensing
Mechanical specifications	
Degree of protection	IP66
Cable	Power supply and data cable: USB 2.0
Length	L max. 1 m
Mass	approx. 250 g
Dimensions	80 mm x 20 mm x 40 mm (W x H x D)
Data for application in connection with hazardous areas	
Certificate	IBExU19ATEXB016X IECEX IBE 19.0026X
Marking	II 3G Ex mc [ic] IIC/IIB T4 Gc II 3D Ex mc [ic] IIIC T135°C Dc
Directive conformity	
Directive 2014/34/EU	EN IEC 60079-0:2018 EN 60079-11:2012 EN 60079-18:2015

Release date: 2022-12-13 Date of issue: 2022-12-13 Filename: 70142704\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".













**Technical Data**

**General information**

Supplementary information

Observe the certificates, declarations of conformity, instruction manuals, and manuals where applicable. For information see [www.pepperl-fuchs.com](http://www.pepperl-fuchs.com).

**Accessories**

	<b>CBL-IDMx6x-DB-J1-S-S30-N0</b>	Serial extension cable for IDM-Zx-* handheld barcode readers
	<b>CBL-IDMx6x-DB-J1-S-S60-N0</b>	Serial extension cable for IDM-Zx-* handheld barcode readers
	<b>CBL-IDMx6x-DB-J1-S-C60-N0</b>	Serial extension cable for IDM-Zx-* handheld barcode readers
	<b>CBL-IDMx6x-DB-J1-S-C30-N0</b>	Serial extension cable for IDM-Zx-* handheld barcode readers
	<b>CBL-IDM160-D-J1-U-C38-N0</b>	Connection cable for IDM-Zx-x6x-D-* corded Handheld Readers
	<b>CBL-IDM160-D-J1-U-S18-N0</b>	Connection cable for IDM-Z1-x6x-D-* corded Handheld Readers
	<b>CBL-IDMx60-D-J1-S-C38-N0</b>	Connection cable for IDM-Z1-x6x-D-* corded Handheld Readers
	<b>CBL-IDMx60-D-J1-S-S18-N0</b>	Connection cable for IDM-Zx-x6x-D-* corded Handheld Readers
	<b>CBL-IDMx61-B-J1-S-S18-N0</b>	Accessory cable for IDM-Zx-x6x-M-* Bluetooth® handheld readers
	<b>CBL-IDMx61-B-J1-U-C38-N0</b>	Accessory cable for IDM-Zx-x6x-M-* Bluetooth® handheld readers
	<b>CBL-IDMx61-B-J1-U-S18-N0</b>	Accessory cable for IDM-Zx-x6x-M-* Bluetooth® handheld readers
	<b>CBL-IDMx61-B-J1-S-C38-N0</b>	Accessory cable for IDM-Zx-x6x-M-* Bluetooth® handheld readers

Release date: 2022-12-13 Date of issue: 2022-12-13 Filename: 70142704\_eng.pdf