




Inductive sensor NAN12-18GM35-I-V1

- Inductive analog sensor
- Output 4 mA ... 20 mA
- Measuring range 0 ... 12 mm
- Non-flush mountable
- Flexible use with versatile mounting opportunities

Inductive distance sensor with analog current output



Dimensions



Technical Data

General specifications

Output type	Analog current output
Installation	non-flush
Output polarity	DC
Actuating element	mild steel, e. g. 1.0037, SR235JR (formerly St37-2) 36 mm x 36 mm x 1 mm
Measuring range	0 ... 12 mm
Output type	3-wire

Nominal ratings

Operating voltage	U_B	15 ... 30 V
Reverse polarity protection		reverse polarity protected
Short-circuit protection		current limited
Linearity error		± 3 % of full-scale value
Temperature drift		± 10 % of full-scale value
Repeat accuracy		± 1 % of full-scale value
Recovery time		≤ 50 ms
No-load supply current	I_0	12 mA
Status indicator		Multihole-LED, yellow permanently on: damping element within measuring range slowly flashing (2 Hz): damping element outside measuring range fast flashing (10 Hz): fault state

Safety-relevant product characteristics

MTTF _d	929 a
-------------------	-------

Release date: 2026-02-27 Date of issue: 2026-02-27 Filename: 70145056-0032_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group
www.pepperl-fuchs.com

USA: +1 330 486 0001
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091
fa-info@sg.pepperl-fuchs.com

PEPPERL+FUCHS


Technical Data

Mission Time (T _M)	20 a
Diagnostic Coverage (DC)	0 %
Analog output	
Output type	4 ... 20 mA
Slope of output characteristic	1.3 mA / mm
Load resistor	≤ 500 Ω
Settling time	≤ 100 ms
Conformity	
PWIS conformity	VDMA 24364-A1/B2/C1/T100°C-W
Compliance with standards and directives	
Standard conformity	
Standards	EN IEC 60947-5-2 EN IEC 60947-5-7
Approvals and certificates	
Protection class	II
Rated insulation voltage	U _i 30 V
Rated impulse withstand voltage	U _{imp} 500 V
UL approval	cULus Listed Load Type: General Purpose Circuitry: Class 2 Power Source Enclosure Type Rating: Type 1 Supply/Switching Voltage: 30 V DC
CCC approval	CCC approval / marking not required for products rated ≤36 V
Ambient conditions	
Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
Storage temperature	-40 ... 85 °C (-40 ... 185 °F)
Mechanical specifications	
Connection type	Connector plug
Housing material	brass , white bronze coated
Sensing face	PBT , green
Degree of protection	IP65/IP67/IP68
Connector	
Threading	M12 x 1
Number of pins	3
Mass	45 g
Dimensions	
Length	51 mm
Diameter	18 mm
Mounting	with nuts, M18
Tightening torque	≤ 30 Nm
General information	
Scope of delivery	2 self locking nuts in scope of delivery

Connection Assignment



Connection Assignment



Wire colors in accordance with EN 60947-5-2

1	BN	(brown)
2	WH	(white)
3	BU	(blue)
4	BK	(black)

Characteristic Curve

