Release date: 2023-10-25 Date of issue: 2023-10-25 Filename: 70141684-100005_eng.pdf

Vibration sensor



VIM82PU-S1B10-20E-I42WV19

- Suitable for SIL2/Pld applications
- Rugged stainless steel housing
- Vibration acceleration in g via root mean square formation (rms)
- Bearing status parameter according to DIN ISO 13373
- 2 relays outputs for safety functions with adjustable switching tresholds, allowing monitoring of a window area

Vibration sensor with safety function both for the analog current output and for the 2 relay outputs with adjustable swichting thresholds










Function

The vibration sensor determines the vibration quantity using rms (root meas square) averaging. This form of quadratic averaging or pre-filtering enables precise trend statements about the condition of the application.

The vibration sensor has a safety integrity level (SIL 2) for usage in functional safety applications.

For monitoring tasks within the scope of functional safety, 2 relay outputs with adjustable switching thresholds are available. With simultaneous evaluation of both relay outputs by a controller, monitoring of a window area is thus possible, e.g. as part of Condition Monitoring. An additional analog current output provides the bearing status parameter weighted according to DIN ISO 13373. This allows a qualitative assessment of the condition of rolling-element bearings.

Dimensions



Technical Data


| General specifications | |
|------------------------|------------------|
| Туре | Vibration sensor |
| Measuring technology | MEMS |

Technical Data

| Series | | Pure Line |
|--------------------------------------|----------------|--|
| Measured variable | | Vibration acceleration |
| | | Bearing status parameter |
| Measurement range | | 0. 40 |
| Vibration acceleration | a- rms | 0 10 g rms |
| Bearing status parameter | | 1 4 see section characteristic curve |
| Measurement accuracy | | ±0.01 g (calibration point: 90% of the measuring range; 159.2 Hz) Complies with the tolerance requirements of DIN ISO 2954 |
| Cross-sensitivity | | <5% of the partial lateral acceleration, which acts exactly 90° to the measuring axis |
| Frequency range | | 10 1000 Hz |
| Averaging time | | for a-rms: 2 s |
| Functional safety related parameters | | |
| Safety Integrity Level (SIL) | | SIL 2 |
| Performance level (PL) | | PL d |
| Category | | Cat. 2 |
| MTTF _d | | 329 a |
| Mission Time (T _M) | | 10 a |
| Diagnostic Coverage (DC) | | min. 90 % |
| Indicators/operating means | | |
| Status indicator | | 6 LEDs for operating states |
| Control elements | | 4 rotary switches and 1 push button for programming |
| Electrical specifications | | |
| Fusing | | external fuse is required: 3 A , semi-time-lag , 30 V DC |
| Operating voltage | U _B | 24 V DC + 7 % / - 10 % |
| Current consumption | | max. 100 mA |
| Power consumption | P_0 | 2.6 W |
| Time delay before availability | t_v | 15 s (initially self-test functions are executed before safe measured values are available at the output) |
| Surge protection | | up to 2 kV |
| Output 1 | | |
| Output type | | relay |
| Switching function | | Normally open (NO) |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 1 A |
| Output 2 | | |
| Output type | | relay |
| Switching function | | Normally open (NO) |
| Switching voltage | | max. 30 V DC |
| Switching current | | max. 1 A |
| Output 3 | | |
| Output type | | analog output, current output of the vibration variable |
| Output current | | 4 20 mA |
| Load resistor | | ≤ 500 Ω |
| Output 4 | | |
| Output type | | analog output, current output of the bearing status parameter |
| Output current | | 4 20 mA (bearing status parameter according to DIN ISO 13373-3, see section characteristic curve) with steps: 1 = 4 8 mA 2 = 8 12 mA 3 = 12 16 mA 4 = 16 20 mA |
| Load resistor | | ≤ 500 Ω |
| Standard conformity | | |
| • | | |

| Technical Data | |
|---|---|
| | |
| Degree of protection | DIN EN 60529, IP66, IP67 |
| Shock resistance | DIN EN 60068-2-27, 60 g, 6 ms |
| Vibration resistance | DIN EN 60068-2-6, 16.5 g, 10 1000 Hz |
| Functional safety | DIN EN IEC 61508 , SIL 2 EN ISO 13849 , PL d |
| Approvals and certificates | |
| UL approval | |
| Ordinary Location | E468231 cULus Listed, Class III Power Source and limited energy, if UL marking is marked on the product. For use in NFPA 70 Applications only. adapters providing field wiring on request |
| Maximum permissible ambient temperature | max. 60 °C (max. 140 °F) |
| Ambient conditions | |
| Ambient temperature | -40 60 °C (-40 140 °F) |
| Measuring head temperature | -40 85 °C (-40 185 °F) directly at the mounting point |
| Storage temperature | -40 60 °C (-40 140 °F) |
| Mechanical specifications | |
| Connection type | plug |
| Housing material | Stainless steel 1.4305 / AISI 303 |
| Housing length | 73.5 mm |
| Housing width | 62 mm |
| Housing height | 46 mm |
| Degree of protection | IP66 / IP67 only in connected state and correctly mounted housing cover |
| Connector | |
| Threading | M12 |
| Number of pins | 8 |
| Mass | approx. 500 g |
| General information | |
| Scope of delivery | 1 x allen head screw M8 x 20 1 x spring washer M8 1 x seal label |

Connection



Accessories

Accessories for this product can be found on the internet at www.pepperl-fuchs.com.

Further Documentation

The sensor manual is also available as detailed overall documentation. Among other things, installation, grounding concepts and mounting are described there in detail.


You can access the manual via the product detail page at www.pepperl-fuchs.com.

Note


The correct electrical connection and the selection of the appropriate grounding concept are crucial for malfunction-free operation of the sensor. For detailed information you may refer to the manual of the sensor.

Characteristic Curve

Bearing status parameter dependent on vibration



Adjustable relay outputs



critical state = out of window (SP1, SP2) = relay is open = like de-energized state